#### **Electrical Specifications**

Model#	MSX-005	MSX-01"	SA-03300	SA-0640	SA-0680	SA-06110
Specified Load Voltage (VId)	3.3V	7.5V	3.6V	7 5 V	7 5 <b>V</b>	7.5V
Typical Current at Vld (Ild)	150mA	150mA	320mA	45mA	90mA	125mA
Open Circuit Voltage (Ioc)	4.6V	10.3V	5 0V	12.0V	12.0V	12.0V
Short Circuit Current (Ioc)	160mA	160mA	380mA	35mA	110mA	150mA
Temperature Coefficient of Voltage per °C	-16mV	-37mV	-15mV	-30mV	-30mV	-30mV
Temperature Coefficient of Current per °C	0.15 mA	0.15mA	0 30mA	0.05mA	0.10mA	0.15mA

# High Temperature Performance

High operating temperature reduces voltage output while slightly improving current As a result, high temperatures may in certain con: tions reduce voltage below to e minimum necessary to charder e a battery. Solarex OEM modules are among the


only commercially available PV devices to minimize this problem. Solarex specifies high Vlds at STC for all its OEM products.

## Mechanical Characteristics and Design Considerations

#### **Active Area**

A Module's Active Area—the frontal area that generates electrical power—is a critical design consid-

eration in u ng any photovoltaic product. If this area is covered by a repunting bezel or hold-down, power may be reduced and the product may cease to function. For optimal performance, the Active Area must never be shaded.



**Front Face of Module** 

Active Area Dimensions									
Туре	A	В	Ċ	D	E	F 🔆			
MSX-005	4.5"	.295"	2.244"	.388"	3 772"	2.830"			
MSX-01	5.0"	230"	4 540"	.409"	4.182"	5.000"			
SA-03300	13.0"	.250"	2.50"	.125"	12.75"	3 000"			
SA-0640	2.16"	.250"	5 50"	.125"	1.91"	6.000"			
SA-0680	4 33"	.250"	5.50"	.125"	4.08"	6 000"			
SA-06110	6.00"	.250"	5 50"	.125"	5 75"	6 000"			

#### Variables Affecting Performance

The current and power output of photovoltaic modules are approximately proportional to illumination intensity. At a given intensity, a photovoltaic module's operating voltage is determined by the characteristics of the load. If that load is a battery, the battery's internal impedance will dictate operating voltage.

Increases in module's temper-

ature increases current but decrease vol age. Solarex's OEM modules are designed to provide peak power roltage that exceeds battery charging requirements in most warm reather conditions.

Care must by taken to assure that Solarex DEM products are properly har illed, finished, installed, ar mounted. Solarex's engineering ervice staff is available for cor. Iltation and support during all phases of product design and manufacturing.

### Maximum Charging Power by Design

Solarex OEM modules are designed to produce maximum power near their specified voltage under load (Vld) points and to produce useful voltage and current over the expected range of operating conditions.

Type	Description	Wire Length	And and II	min.) 🗅	Ild(typ.)	Length*	-/ Width*	Thickness
MSX-005	MEGA module with wires	6.0"(152.4mm)	3.3V	5mA	150mA	4.50"(114.3mi	n) 2.63"(66.8mm)	.125"(3.0mm)
MSX-01	MEGA module with wires	6.0"(152.4mm)	7.5V	5mA	150mA	5.00"(127.0mi	m) 5.00"(127.0mm)	.125"(3.0mm)
Solarex	SÃ-Series Plate	Products (m	ultiple co	pone	nts on 1	2" by 13" pl	lates)	
Туре 🔭 🎉 👢	Description 4	Components/Plate	(Vid. 11	min.).	Ild(typ-)	Length*	. Width	Thickness*
SA-03300P	Finished 4X Plate	4	3.6V :	0mA	320mA	13.00"(330.2m	im) 3.00"(76.2mm)	.090"(2.3mm)
SA-06110P	Standard 4X Plated	4	7.5V	0mA	125mA	6.00"(152.4mi	m) 6.00"(152.4mm)	.090"(2.3mm)
SA-06110P	Coated 4X Plate	4	7.5V	0mA	125mA	6.00"(152.4mi	m) 6 00"(152.4mm)	.090"(2.3mm
SA-Serie	s Components (	individual co	omponent	ready	to use)	,		
Гуре	Description	Vid.	Ild(min.)	Nd(typ.)	441	ength*	Width*	Thickness*
SA-03300	Finished Component	3.6V	300mA	320mA	13.00	)"(330.2mm)	3.00"(76.2mm)	.090"(2.3mm)
SA-0640	Standard Component	7.5V	40mA	45mA	6.00	"(152.4mm)	2.17"(55.1mm)	.090"(2.3mm)
SA-0680	Standard Component	7.5V	80mA	90mA	6.00	"(152.4mm)	4.33"(110.0mm)	.090"(2.3mm)
SA-06110	Standard Component	7.5V	110mA	125mA	6.00	"(152.4mm)	6.00"(152.4mm)	090"(2.3mm)
SA-I	Wired Component	17.5V	80mA	100mA	12.00	)"(304.8mm)	4.33"(110.0mm)	.090"(2.3mm
SA-2	Wired Component	7.5V	290mA	325mA	13.00	)"(330.2mm)	6.00"(152.4mm)	.090"(2.3mm
SA-5	Wired Component	17.5V	290mA	325mA	13.00	)"(330.2mm)	12.00"(304.8mm)	.090"(2.3mm

- "Coated" SA-Series plates and components are provided with a protective back coating.
   "Finished" SA-Series plates and components are provided with a protective coating and solder pads.
- STC Standard Test Conditions are illumination of 1kW/r (1 sun) at spectral distribution 1.5 and a solar cell temperature of 25°C.

• Ild (min.) - Minimum initial current output measured at V ander STC (Standard Test Conditions).

• Ild (typ.) - Typical initial current output measured at Vld ui er STC.
• "Standard" SA-Series plates and components are provided ithout a protective back coating and solder pads.

\*All plate products are 12" x 13" x . 09" (304.8 mm x 330 2 mm x 2.3 mm)