

CHEMTRONICS®

Technical Data Sheet

TDS # 2279

Max-Kleen™ Lectro-Solv™

The extra-strength, nonflammable heavy-duty degreaser with high dielectric

PRODUCT DESCRIPTION

Max-Kleen™ Lectro-Solv™ is ideal for removal of all types of soils including oxidized oil and grease from electrical motors and equipment. It is the ideal solvent for most electrical applications. This extra-strength degreaser evaporates quickly without leaving a residue behind. Max-Kleen™ Lectro-Solv™ is registered with the NSF as a K1, K2 cleaner/degreaser for use in food processing facilities.

- Best product for electrical applications
- Quickly removes all types of tough soils including oxidized oil and grease
- NSF K1, K2 registered
- Dielectric strength of 30 kV
- Contains trichloroethylene
- Nonflammable, no flash point
- Non-corrosive and non-conductive
- Leaves no residue
- Ozone safe

TYPICAL APPLICATIONS

Max-Kleen™ Lectro-Solv™ can be used for all repair, maintenance, and manufacturing applications including:

- Removes grease, oil, lubricants, wax and tar
- Cleans contacts, relays and switches, circuit breakers and fuse blocks
- All repair and maintenance cleaning including: controls, conveyors and gear drives
- Cleans electric motors and gasoline engines
- Removes tough soils from gears and pulleys
- Use for maintenance of air compressors

TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

Boiling Point	189° F (Initial)
Evaporation Rate (butyl acetate=1)	>1
Flash Point (TCC)	None
Specific Gravity	1.46
Vapor Pressure @68°F	60 mmHg
Appearance	Clear, colorless liquid
Odor	Mild
Solubility in Water	Negligible
Dielectric Breakdown (ASTM D-877)	30 kV
Kauri-Butanol (KB) Number	128
VOC content (Not for Sale in California)	100%
Shelflife	5 years
NSF-Registered K1, K2	#139460 (aerosol) #139461 (bulk)

COMPATIBILITY

Max-Kleen™ Lectro-Solv™ is compatible with most metals. As with any solvent, compatibility with plastics should be determined on a non-critical area prior to use. Materials such as polystyrene, ABS, polycarbonate and PVC are not compatible with the cleaning solvent in Max-Kleen™ Lectro-Solv™.

Material**Compatibility**

ABS	Poor
Buna-N	Poor
EPDM	Not Recommended
Graphite	Excellent
HDPE	Fair
PVDF	Excellent
LDPE	Poor
Lexan™	Poor
Neoprene	Poor
Noryl®	Poor
Nylon™ 66	Fair
Polycarbonate	Poor
Polypropylene	Fair
Polystyrene	Not Recommended
PVC	Poor
Silicone Rubber	Poor
Teflon™	Excellent
Viton™	Excellent

AVAILABILITY

ES2279	19 oz aerosol
ES179	1 gallon liquid
ES5579	55 gallon liquid

SAFETY & ENVIRONMENTAL DATA

SAFETY & ENVIRONMENTAL DATA			
CFC	0.0%	VOC	100%
HCFC-225	0.0%	HFC	0.0%
HCFC-141b	0.0%	nPB	0.0%

NOTE:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. ITW CHEMTRONICS® does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Chemtronics® is a registered trademark of ITW Chemtronics. All rights reserved. Max-Kleen™, Lectro-Solv™ and Controlwipes™ are trademarks of ITW Chemtronics. All rights reserved. All other trademarks herein are trademarks or registered trademarks of their respective owners.

MANUFACTURED BY:

ITW CHEMTRONICS®
 8125 COBB CENTER DRIVE
 KENNESAW, GA 30152
 1-770-424-4888 REV C (09/20/07)

DISTRIBUTED BY:**USAGE INSTRUCTIONS****Read MSDS carefully prior to use.**

Spray 4-6 inches from surface to clean. Wash parts from top to bottom, allowing the liquid to flush away dirt and dissolved grease. For precise application use attached extension tube.

Dip applications - Allow the soiled article to soak in Max-Kleen™ Lectro-Solv™ for 5 - 10 minutes, then remove and loosen any remaining soils with a Controlwipes™ Wipe.

For wipe applications, wet a Controlwipes™ Wipe with Max-Kleen™ Lectro-Solv™ and wipe away soils.

When used to clean food equipment that will be returned to a food processing area, wash well with an acceptable detergent solution and rinse thoroughly with potable water.

TECHNICAL & APPLICATION ASSISTANCE

ITW Chemtronics® provides a technical hotline to answer your technical and application related questions. The toll free number is:

1-800-TECH-401.