



[HOME](#) [PRODUCTS](#) [WHERE TO BUY](#) [REGISTRATION](#) [SUPPORT](#) [FAQS](#) [MANUALS](#) [DRIVE](#)

**NISIS POCKET DV4 DIGITAL VIDEO CAMERA**

The NISIS Pocket DV4 Camera is a :-

- Digital Camcorder
- Digital Still Camera
- Web Cam
- Voice Recorder
- MP3 Player
- USB portable disc

It measures only 4.2" x 2.7" x 1.6" but packs an incredible number of features, such as a 2 Megapixels image sensor, SD/MMC Card slot to accept Cards of up to 256 MB (not included), 1.5" colour TFT LCD display, 16 MB of built-in Flash memory and much more.

You can view your recorded movies and still photographs on your television, if your TV has A/V inputs, and you can also upload them to your computer where you can edit and send them to your friends on the Internet.

The Pocket DV4 camera comes with a mini tripod, a carrying strap, A/V leads, a USB cable, rechargeable batteries\*, a mains battery charger\*, earphones, soft carrying bag and an Installation CD that includes useful applications to help you create professional looking movies and still photographs.

The Pocket DV4 Camera offers the ability to enhance the resolution of still photographs to 2048 x 1536 pixels (3 Mega pixels), and 2272 x 1704 pixels (4 Mega pixels), using a technique known as firmware interpolation. This enables you to print enlargements of your favourite photographs, and maintain picture sharpness up to paper sizes in excess of A4 size.

\* UK version only.



FEATURES	SPECIFICATIONS																
<ul style="list-style-type: none"> <li>● Records video with sound</li> <li>● Takes still photographs</li> <li>● Records audio clips</li> <li>● Plays MP3 music files</li> <li>● Operates as a web cam</li> <li>● Use as a USB portable disc</li> <li>● 1600 x 1200 (2 Mega) pixels CMOS colour sensor</li> <li><b>Still photograph resolutions:-</b> <ul style="list-style-type: none"> <li>○ 1600 x 1200 (2 Mega) pixels</li> <li>○ 2048 x 1536 (3 Mega) pixels (Firmware interpolation)</li> <li>○ 2272 x 1704 (4 Mega) pixels (Firmware interpolation)</li> </ul> </li> <li><b>Video Movie resolutions:-</b> <ul style="list-style-type: none"> <li>○ 320 x 240 pixels - up to 20 fps</li> <li>○ 640 x 480 pixels - up to 10 fps</li> </ul> </li> <li><b>PC Camera resolutions:-</b> <ul style="list-style-type: none"> <li>○ 320 x 240 pixels - up to 20 fps</li> <li>○ 640 x 480 pixels - up to 10 fps</li> </ul> </li> <li>● Built-in 1.5" colour TFT LCD screen</li> <li>● 16 MB of built-in Flash memory</li> <li>● Expandable Memory with SD/MMC Cards up to 256 MB (not supplied)</li> <li>● Focus: Close-up. 30 - 40 cm; Normal. 40 cm to infinity</li> <li>● 4 x Digital Zoom</li> <li>● Playback video and pictures on your television*</li> <li>● Includes tripod</li> <li>● Built-in speaker for audio playback</li> <li>● Built-in microphone</li> <li>● Edit uploaded videos and still photographs</li> <li>● Email video clips and pictures to friends and family</li> <li>● Self timer built-in</li> <li>● Built-in Flash light</li> <li>● Includes carrying strap and soft case</li> <li>● Mains Battery Charger and 4 x rechargeable batteries included**</li> <li>● USB and A/V cables included</li> <li>● Bundled with video &amp; still photos editing software</li> </ul> <p>* Requires television with A/V input sockets. ** UK version only.</p>	<p><b>Multifunctions</b></p> <ul style="list-style-type: none"> <li>● Digital Still Camera mode</li> <li>● Video Recording mode</li> <li>● Voice Recording mode</li> <li>● Web Cam mode</li> <li>● MP3 Playback mode</li> <li>● USB portable disc mode</li> </ul> <p><b>Still Image Resolution</b></p> <ul style="list-style-type: none"> <li>● 1600 x 1200 (2 Mega) pixels</li> <li>● 2048 x 1536 (3 Mega) pixels (Firmware Interpo</li> <li>● 2272 x 1704 (4 Mega) pixels (Firmware Interpo</li> </ul> <p><b>Digital Video Camcorder Resolution</b></p> <ul style="list-style-type: none"> <li>● 640 x 480 pixels - up to 10 fps</li> <li>● 320 x 240 pixels - up to 20 fps</li> </ul> <p><b>PC Camera Resolution</b></p> <ul style="list-style-type: none"> <li>● 640 x 480 pixels - up to 10 fps</li> <li>● 320 x 240 pixels - up to 20 fps</li> </ul> <p><b>Image Sensor</b></p> <ul style="list-style-type: none"> <li>● 1600 x 1200 (2 Mega) pixels colour CMOS</li> </ul> <p><b>LCD</b></p> <ul style="list-style-type: none"> <li>● 1.5" Colour TFT LCD Display</li> </ul> <p><b>Internal Memory</b></p> <ul style="list-style-type: none"> <li>● 16 MBytes built-in Flash memory</li> </ul> <p><b>External Memory</b></p> <ul style="list-style-type: none"> <li>● Built-in SD/MMC Card slot</li> <li>● Accepts SD/MMC Cards up to 256 MB (Not inclu</li> </ul> <p><b>Camera Capacity based on a 64 MB SD Card (n</b></p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="text-align: center;">Mode</th> <th style="text-align: center;">Condition</th> </tr> </thead> <tbody> <tr> <td rowspan="3" style="text-align: center; vertical-align: middle;">Digital Video (DV)</td> <td style="text-align: center;">VGA (640 x 480)</td> </tr> <tr> <td style="text-align: center;">QVGA (320 x 240)</td> </tr> <tr> <td style="text-align: center;">Normal Fine Best</td> </tr> <tr> <td rowspan="5" style="text-align: center; vertical-align: middle;">Camera</td> <td style="text-align: center;">640 x 480</td> </tr> <tr> <td style="text-align: center;">1600 x 1200</td> </tr> <tr> <td style="text-align: center;">2048 x 1536</td> </tr> <tr> <td style="text-align: center;">2272 x 1704</td> </tr> <tr> <td style="text-align: center;">Normal Fine</td> </tr> <tr> <td style="text-align: center;">Voice Recording (VR)</td> <td style="text-align: center;">-</td> </tr> <tr> <td style="text-align: center;">MP3</td> <td style="text-align: center;">Average 4MB per track</td> </tr> </tbody> </table> <p><b>Self Timer</b></p> <ul style="list-style-type: none"> <li>● 10 seconds</li> </ul> <p><b>Image Formats</b></p> <ul style="list-style-type: none"> <li>● JPEG for still photographs</li> <li>● AVI for Video recordings</li> </ul> <p><b>Focus</b></p> <ul style="list-style-type: none"> <li>● Close up: 30 to 40 cm</li> </ul>	Mode	Condition	Digital Video (DV)	VGA (640 x 480)	QVGA (320 x 240)	Normal Fine Best	Camera	640 x 480	1600 x 1200	2048 x 1536	2272 x 1704	Normal Fine	Voice Recording (VR)	-	MP3	Average 4MB per track
Mode	Condition																
Digital Video (DV)	VGA (640 x 480)																
	QVGA (320 x 240)																
	Normal Fine Best																
Camera	640 x 480																
	1600 x 1200																
	2048 x 1536																
	2272 x 1704																
	Normal Fine																
Voice Recording (VR)	-																
MP3	Average 4MB per track																
SOFTWARE INCLUDED																	
<div style="display: flex; align-items: flex-start;"> <div> <p><b>CyberLink PowerDirector Pro</b> Edit and Create Movies on CDs <a href="#">More info</a></p> </div> </div> <div style="display: flex; align-items: flex-start; margin-top: 10px;"> <div> <p><b>CyberLink Media Show SE</b> Make Animated Slideshows for the Web or Screensavers <a href="#">More info</a></p> </div> </div>																	



**CyberLink VideoLive Mail**  
Create and Send Video E-Mails  
[More info](#)



**Ulead Photo Explorer**  
Visual File Management Software  
[More info](#)



**Ulead Photo Express**  
Edit and Create Exciting Illustrations & Photos  
[More info](#)

- Normal: 40 cm to infinity
- Zoom control**
  - Digital x 4
- Image Control**
  - Auto exposure and auto white balance
- Computer Interface**
  - USB 1.1 & 2.0
- Flash**
  - Auto, On or Off
- White Balance**
  - Auto, Sunny, Cloudy, Fluorescent or Tungsten
- Exposure Control**
  - 2 modes: Auto and Manual -3 to +3 (7 levels)
- Power Saving**
  - Auto power off idle time, User selectable
- Power Source**
  - 4 x AA NiMH rechargeable batteries (included\*)
  - USB port when plugged into PC
- Camera Dimensions**
  - 107 x 69 x 40 mm (4.2" x 2.7" x 1.6")

\* UK version only

**MINIMUM SYSTEM REQUIREMENTS**

- Pentium II 266 MHz. Processor or faster
- 64MB RAM (128MB recommended)
- Display adapter with at least 4MB RAM displaying at least 16-bit colour
- 4 x Speed CD-ROM or DVD Drive
- Windows 98SE, ME, 2000 or XP
- Not compatible with Apple Mac computers
- Spare USB 1.1 or 2.0 Port
- DirectX version 8.0 or later

**OTHER NISIS DIGITAL VIDEO CAMERAS**



Copyright © 2001-2004 Netway Components Ltd. /