


1-800-383-7323 USA/CAN www.energizer.com

SILVER OXIDE

ENERGIZER 373



Industry Standard Dimensions



0.03 (0.001) Minimum Ref. (applies to top edge of gasket or edge of crimp, whichever is higher)

DESIGNED FOR USE ON CONTINUOUS LOW DRAIN

Specifications

Chemical System: Silver Oxide (Zn/Ag₂O)

Designation: IEC-SR68 **Nominal Voltage:** 1.55 Volts

Typical Capacity: 30 mAh* (to 1.3 volts)


Capacity Test: 30K ohm continuous drain at 21°C

Typical Weight: 0.50 grams (0.016 oz.)

Typical Volume: 0.12 cubic centimeters (0.007 cubic inch)

Impedance (40 Hz): 40 to 50 ohms


Cross Section



Typical Discharge Characteristics

Typical Performance at 21°C (70°F)


Schedule: Continuous Typical Drain @1.55V: 0.052 milliamperes Load: 30K ohm




<u>Schedule</u>	<u>Typical Drains</u> at 1.55V	<u>Load</u>	Cutoff 1.3V
	(milliamperes)	(ohm)	(hours)
Continuous	0.052	30K	577

Temperature Characteristics

Typical Performance at Low Discharge Rates





Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4328E Page 1 of 1

^{*} Varies according to the applied load, temperature, and cutoff voltage.