

Calipers



Electronic calipers do the work of dial calipers with added benefits. High-contrast liquid crystal display provides easy, instant readings with no need for calculations. Microprocessor-based calipers convert

from inch to metric at the push of a button. General's high quality, easy-to-read dial calipers make precise inside, outside, depth and step measurements.



147



No. 146 Digital Display



No. 147 Fractional Display

FRACTION+

DIGITAL FRACTIONAL CALIPERS

- No. 147, No. 1478, No. 14712 are Heavy Duty Stainless Steel Construction.
- No. 146 has a Non-Marring Plastic Housing.
- Convenient Auto On/Off Feature.
- Three Mode Digital Display: Decimal Inches, Fractions, Metric.
- Accuracy: +/- 0.001" +/- 0.02mm.
- Resolution: 0.0005", 0.01mm, 1/64".
- Includes: 1 "LR44/357" battery.

UPC	NO.	RANGE
01460 3	146	0 - 6" (0 - 153mm)
01470 2	147	0 - 6" (0 - 153mm)
01478 3	1478	0 - 8" (0 - 203mm)
14712 7	14712	0 - 12" (0 - 305mm)

MACHINIST

6" ELECTRONIC DIGITAL, STAINLESS STEEL CALIPER

- Accurately reads to .001".
- Large, easy-to-read numbers.
- Instantly convert inches to millimeters and back again.
- Hardened stainless steel construction for durability and corrosion resistance.
- Satin finished scale with etched black graduations for easy reading.
- "Zero" button for two-step measurements without calculations.

- Inside, outside, depth, and step measurement.
- Freewheeling friction roller for repetitive and accurate readings.
- Lock for repetitive measurement.
- Includes "LR44" battery and instructions, packaged in a sturdy, fitted, foam-lined plastic case designed specifically for this tool.



1436

UPC	NO.	CAPACITY
14360 0	1436	0 - 6" (0 - 153mm)

6" ELECTRONIC DIGITAL CALIPER

- Fiberglass reinforced plastic gives precision measurements at an economical price.
- Accurate digital measurements in both inches, metric & fractional.
- Freewheeling friction roller for repetitive and accurate readings.
- Measuring capacity 0 - 6" (150mm).

- Inside, outside, depth and step measurement.
- Swiss precision crafted.
- Direct reading .0005/.01mm.
- Accuracy 0.001"/0.1mm.
- Adjustable zero.
- Includes "LR44" battery.




143

UPC	NO.
22064 6	143

6" DIAL CALIPER

- Stainless steel construction for accuracy and durability.
- Large, clear dial accurately reads to .001".
- Satin chrome scale with clearly etched tenths of inch graduations.
- Covered rack ensures smooth operation by preventing dirt and chips from entering rack and gear mechanism.

- Inside, outside, depth and step measurement.
- Lock for repetitive measurement.
- Free wheeling thumb roller.
- Depth stop rod.
- Adjustable bezel for zero setting.



107

UPC	NO.	CAPACITY
10700 8	107	0 - 6" (0 - 153mm)

DIAL CALIPER AND MARKING SET

- This set contains three of the most useful measuring and marking tools for mechanics and machinists.
- Set includes: 6" Dial Caliper; 6" x 3/4" Stainless Steel Ruler with satin finish and reversible Tip Carbide Scriber with magnetic pick-up.
- Ruler has etched and filled 4R graduations (1/8", 1/16", 1/32", 1/64").

- Scriber has aluminum body with knurled handle in an overall length of 4-3/4".
- Caliper has inside, outside, depth and step measurement.
- Caliper has lock for repetitive measurement.
- Free wheeling thumb roller.
- Packaged in a sturdy, fitted, plastic case designed specifically for this set.



108

UPC	NO.
10800 5	108

