

Fire Extinguishers



fire extinguishers



fire blankets





Turbo Spray



A specially formulated additive that dramatically increases water's fire fighting capability in three ways:

- Cooling effect as with water
- Chemical reaction creating rapid knock down
- Sealing action reducing the risk of re-ignition

Lightweight

The three litre Turbospray has a 13A fire rating, which is the same performance as an ordinary nine litre water, so providing a 100% weight advantage. Being smaller and lighter it is easier to use when weight is an important consideration.

An additional feature of the nozzle is that it enables this range to pass the 35Kv conductivity test and allows them to be safe if used on fire risks in the close proximity of live electrical equipment.

Specification

Operation: Squeeze grip - Controllable discharge.
 Manufactured to BS EN3:1996 BSI Kitemark and 

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|--------|-------|--------|------------------|
| ANT03104 | 3 Litres | 432mm x 161mm | 5.9kg | 3m | 25secs | 13A |
| ANT06104 | 6 Litres | 533mm x 181mm | 10.4kg | 4m | 60secs | 21A |

Water



Ordinary combustable materials

Water extinguishers are suitable for class A fires involving carbonaceous materials such as burning wood, paper, cloth etc. Water extinguishes by cooling the fire, so that insufficient heat remains to sustain burning and prevents glowing embers from re-kindling.

Specification

Operation: Squeeze grip - Controllable discharge.
 Manufactured to BS EN3:1996 BSI Kitemark and 

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|--------|-------|--------|------------------|
| ANW09104 | 9 Litres | 620mm x 200mm | 14.3kg | 7m | 60secs | 13A |
| ANW09004 | 9 Litres | 620mm x 200mm | 15kg | 7m | 56secs | 13A |



Tri-Class Foam



Ordinary combustable materials and flammable liquids

Ideal for situations where both class A and class B fire risks are likely to be found. Tri-class Foam extinguishers containing Aqueous Film Forming Foam (AFFF) are particularly suitable for class B type fires involving flammable liquids such as burning petrol, oil, fats, solvents and paints, but are also the equal of water for ordinary combustibles.

The unique jet/spray nozzle ensures a good throw of foam which provides rapid fire knockdown and has a blanketing effect which both smothers the flame and prevents re-ignition of flammable vapours by sealing the surface of the material. An additional feature of the nozzle is that it enables this range to pass the 35Kv conductivity test and allows them to be safe if used on fire risks in the close proximity of live electrical equipment.

Specification

Operation: Squeeze grip - Controllable discharge.
Manufactured to BS EN3:1996 BSI Kitemark and **CE**

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|--------|-------|----------|------------------|
| ANF01104 | 1 Litre | 320mm x 80mm | 1.5kg | 2.3m | 14secs | 5A 21B |
| ANF02104 | 2 Litres | 450mm x 108mm | 3.2kg | 4.5m | 21.4secs | 8A 55B |
| ANF03104 | 3 Litres | 432mm x 161mm | 5.8kg | 5m | 13secs | 8A 70B |
| ANF06104 | 6 Litres | 533mm x 180mm | 10.5kg | 5m | 36secs | 13A 183B |
| ANF09104 | 9 Litres | 610mm x 200mm | 14.5kg | 5m | 53secs | 21A 183B |
| ANF06004 | 6 Litres | 506mm x 180mm | 10.7kg | 5m | 26secs | 13A 183B |
| ANF09004 | 9 Litres | 620mm x 200mm | 14.9kg | 5m | 49secs | 21A 183B |

Multi-Purpose Dry Powder



Ordinary combustable materials, flammable liquids, flammable gas

Multi-Purpose Dry Powder Fire Extinguishers are a safe, versatile and easily used medium suited to all high risk environments or where the fire hazards are mixed. They are particularly suited to spillages of flammable liquids and fires involving flammable gases such as propane and butane. They are ideal for fires in vehicles.

ABC Powder is a non conductor of electricity and will provide the operator with a heat shield and extremely fast knockdown.

Specification

Operation: Squeeze grip - Controllable discharge.
Manufactured to BS EN3:1996 BSI Kitemark and **CE**

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|--------|-------|----------|------------------|
| ANP01104 | 1kg | 280mm x 90mm | 1.5kg | 4m | 8secs | 5A 34B C |
| ANP02104 | 2kg | 327mm x 110mm | 3.2kg | 4m | 9.5secs | 13A 89B C |
| ANP04104 | 4kg | 415mm x 160mm | 6.7kg | 6m | 12secs | 21A 113B C |
| ANP06104 | 6kg | 505mm x 160mm | 9.1kg | 6m | 16secs | 27A 183B C |
| ANP09104 | 9kg | 603mm x 180mm | 13.6kg | 7m | 16secs | 43A 233B C |
| ANP01214 | 12kg | 590mm x 200mm | 16.9kg | 7m | 20secs | 55A 233B C |
| ANP04004 | 4kg | 448mm x 160mm | 7.3kg | 5m | 14.5secs | 21A 113B C |
| ANP06004 | 6kg | 527mm x 160mm | 9.9kg | 6m | 21secs | 27A 144B C |
| ANP09004 | 9kg | 595mm x 180mm | 14.1kg | 6m | 26secs | 43A 233B C |

BC, Monnex and Metal Fire Powder also available.



Carbon Dioxide



Flammable liquids and electrical/electronic hazards

CO₂ Gas is ideal for use in modern office environments for all electronic risks such as computers, photocopiers and in manufacturing industries where oils, spirits, solvents and other flammable materials are used.

The gas is inert and non-damaging, showing no trace after dispersal.

Specification

Operation: Squeeze grip - Controllable discharge.

Manufactured to BS EN3:1996

BSI Kitemark and **CE**

Cylinders conform to BS 5045: Part 8: 2000

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|---------|-------|--------|------------------|
| ANC02106 | 2kg | 535mm x 111mm | 4.74kg | 3m | 12secs | 34B |
| ANC05105 | 5kg | 670mm x 152mm | 10.85kg | 3m | 15secs | 55B |

Fryguard Wet Chemical



Flammable liquids specifically cooking oils and fats

Fryguard is a wet chemical which has been designed specifically to tackle fires involving high temperature cooking oils and fats which cannot be successfully tackled using conventional extinguishants.

BS 7937:2000 established a new Class F classification for fires involving cooking oils. Fryguard wet chemical is delivered as a fire spray via a long lance. On contact with the oil or fat it saponifies, causing a thick impenetrable blanket to form, rapidly extinguishing the fire.

Specification

Operation: Squeeze grip - Controllable discharge.

Manufactured to BS 7937:2000

BSI Kitemark and **CE**

| Model no. | Capacity | Dimensions | Weight | Range | Time | Fire Test Rating |
|-----------|----------|---------------|--------|-------|--------|------------------|
| ANF16104 | 6 Litres | 650mm x 180mm | 12.1kg | 5m | 35secs | 13A 75F |

Fire Blankets

Fire Blankets offer a highly cost effective means of providing primary protection on small localised fires in kitchens, laboratories, workshops etc.

Manufactured to BS EN1867:1997 and supplied in a neat PVC container with quick release action.

| Model no. | Dimensions |
|-----------|-----------------|
| CNA 01108 | 1000mm x 1000mm |
| CNA 02208 | 1200mm x 1200mm |
| CNA 07708 | 1800mm x 1200mm |
| CNA 02808 | 1800mm x 1750mm |