

2.5x5mm RECTANGULAR SOLID LAMP

WP383GDT

GREEN


Features

- LOW POWER CONSUMPTION.
- RELIABLE AND RUGGED.
- EXCELLENT UNIFORMITY OF LIGHT OUTPUT.
- SUITABLE FOR LEVEL INDICATOR.
- LONG LIFE SOLID STATE RELIABILITY.
- RoHS COMPLIANT.

Description

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

Package Dimensions



Notes

- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.25 (0.01")$ unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAF0512 REV NO: V.2 DATE: APR/21/2005 PAGE: 1 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003858

Kingbright

Selection Guide

Part No.	Dice	Lens Type	lv (mcd) @ 10mA		Viewing Angle
			Min.	Тур.	201/2
WP383GDT	GREEN (GaP)	GREEN DIFFUSED	1	4	110°

Note:

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF	Forward Voltage	Green	2.2	2.5	V	IF=20mA
IR	Reverse Current	Green		10	uA	VR = 5V

Absolute Maximum Ratings at Ta=25°C

Parameter	Green	Units			
Power dissipation	105	mW			
DC Forward Current	25	mA			
Peak Forward Current [1]	140	mA			
Reverse Voltage	5	V			
Operating/Storage Temperature	-40°C To +85°C	-40°C To +85°C			
Lead Solder Temperature [2]	folder Temperature [2] 260°C For 3 Seconds				
ead Solder Temperature [3] 260°C For 5 Seconds					


Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAF0512 REV NO: V.2 DATE: APR/21/2005 PAGE: 2 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003858


^{1.} θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.


Kingbright



SPEC NO: DSAF0512 REV NO: V.2 DATE: APR/21/2005 PAGE: 3 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003858

Kingbright





Remarks

If special sorting is required (e.g. binning based on forward voltage, luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: +/-1nm

2. Luminous Intensity: +/-15%

3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAF0512 REV NO: V.2 DATE: APR/21/2005 PAGE: 4 OF 4
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: S.H.CHEN ERP:1101003858