10mm SOLID STATE LAMP

WP813ID HIGH EFFICIENCY RED Description **Features** •10mm DIAMETER BIG LAMP. The High Efficiency Red source color devices are •I.C. COMPATIBLE. made with Gallium Arsenide Phosphide on Gallium Phosphide Orange Light Emitting Diode. •RELIABLE AND RUGGED. •LONG LIFE - SOLID STATE RELIABILITY. •RoHS COMPLIANT. **Package Dimensions** 13.5(.531) 27(1.063)MIN ø11(.433) 2(.079)1.5(.06)TYP CATHODE ø10(.394) 54(0.1) 3 5 0.7MAX. □ 0.5(0.02) ±0.05 1.0 MAX. Notes: 1. All dimensions are in millimeters (inches). 2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted. 3. Lead spacing is measured where the leads emerge from the package. 4. Specifications are subject to change without notice.

REV NO: V.2 CHECKED: Allen Liu DATE: APR/19/2005 DRAWN: S.H.CHEN PAGE: 1 OF 4 ERP: 1101007548

Selection Guide								
Part No.	Dice	Lens Type	lv (mcd) @ 20mA		Viewing Angle			
			Min.	Тур.	2 θ 1/2			
WP813ID	HIGH EFFICIENCY RED (GaAsP/GaP)	RED DIFFUSED	36	100	60 °			

Note:

1. θ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	High Efficiency Red	627		nm	IF=20mA
λD	Dominant Wavelength	High Efficiency Red	625		nm	I⊧=20mA
Δλ1/2	Spectral Line Half-width	High Efficiency Red	45		nm	IF=20mA
С	Capacitance	High Efficiency Red	15		pF	VF=0V;f=1MHz
Vf	Forward Voltage	High Efficiency Red	2.0	2.5	V	IF=20mA
IR	Reverse Current	High Efficiency Red		10	uA	VR = 5V

Absolute Maximum Ratings at TA=25°C


Parameter	High Efficiency Red	Units	
Power dissipation	105	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	160	mA	
Reverse Voltage	5	V	
Operating/Storage Temperature	-40°C To +85°C		
Lead Solder Temperature [2] 260°C For 3 Seconds			
Lead Solder Temperature [3] 260°C For 5 Seconds			

Notes:


1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.

3. 5mm below package base.



REV NO: V.2 CHECKED: Allen Liu DATE: APR/19/2005 DRAWN: S.H.CHEN PAGE: 3 OF 4 ERP: 1101007548



REV NO: V.2 CHECKED: Allen Liu DATE: APR/19/2005 DRAWN: S.H.CHEN PAGE: 4 OF 4 ERP: 1101007548