



# BITS AND NUT SETTERS

AIMCO has assembled the most complete package of commonly used screwdriver bits and nut setters in the industry. Our goal is to supply you with the highest quality bits and nut setters for all your fastener needs. If you're in the electronics, aerospace or general industry, AIMCO has the bits and nut setters to fit your needs.



Most items are available in both American and Japanese industrial standards to properly fit your fasteners.



Made to order specials are available upon request.

# PHILLIPS® POWER BITS


Puntas Phillips®



Part No.	Point Size	Length	
		mm	in
A3S0-2	0	50	1.969
A3S1-2	1	50	1.969
A3S1-2.75	1	70	2.756
A3S1-3	1	75	2.953
A3S1-3.5	1	90	3.543
A3S1-4	1	100	3.938
A3S1-6	1	150	5.906
A3S2-1.2	2	30	1.181
A3S2-1.6	2	40	1.574
A3S2-2	2	50	1.969
A3S2-2.75	2	70	2.756
A3S2-3	2	75	2.953
A3S2-3.5	2	90	3.543
A3S2-4	2	100	3.938
A3S2-4.7	2	120	4.724
A3S2-4.75	2	125	4.921
A3S2-6	2	150	5.906
A3S2-8	2	200	7.874
A3S2-10	2	250	9.842
A3S2-12	2	300	11.811
A3S3-2	3	50	1.969
A3S3-2.75	3	70	2.756
A3S3-3	3	75	2.953
A3S3-3.5	3	90	3.543
A3S3-4	3	100	3.938
A3S3-4.7	3	120	4.724
A3S3-6	3	150	5.906
A3S3-8	3	200	7.874
A3S3-10	3	250	9.842
A3S3-12	3	300	11.811


# SLOTTED POWER BITS

Puntas Agujereadas



Part No.	Screw Size	Length		Blade Thickness	Blade Width
		mm	in		
A3M8-2	8	50	1.969	.042	0.275
A3M8-2.75	8	70	2.756	.042	0.275
A3M8-3	8	75	2.953	.042	0.275
A3M10-2	10	50	1.969	.046	0.312
A3M10-2.75	10	70	2.756	.046	0.312
A3M10-3	10	75	2.953	.046	0.312
A3M12-2	12	50	1.969	.050	0.360
A3M12-2.75	12	70	2.756	.050	0.360
A3M12-3	12	75	2.953	.050	0.360




Reduced Diameter  
Puntas Ranurados Con Diametro Reducido



Part No.	Screw Size	Length		Blade Thickness	Blade Width
		mm	in		
A3MT1-2	1	50	1.969	.022	0.122
A3MT1-3	1	75	2.953	.022	0.122
A3MT3-2	3	50	1.969	.030	0.154
A3MT3-3	3	75	2.953	.030	0.154
A3MT4-2	4	50	1.969	.034	0.188
A3MT4-2.75	4	70	2.756	.034	0.188
A3MT4-3	4	75	2.953	.034	0.188
A3MT5-2	5	50	1.969	.036	0.250
A3MT5-2.75	5	70	2.756	.036	0.250
A3MT5-3	5	75	2.953	.036	0.250
A3MT6-2	6	50	1.969	.038	0.250
A3MT6-2.75	6	70	2.756	.038	0.250
A3MT6-3	6	75	2.953	.038	0.250

# SLOTTED INSERT BITS


Insertos Ranurados



Part No.	Screw Size	Length		Blade Thickness	Blade Width
		mm	in		
A38M2-1	2	25	0.984	0.026	0.281
A38M2-1.5	2	38	1.496	0.026	0.138
A38M3-1	3	25	0.984	0.030	0.154
A38M3-1.5	3	38	1.496	0.030	0.154
A38M4-1	4	25	0.984	0.030	0.170
A38M4-1.5	4	38	1.496	0.034	0.188
A38M5-1	5	25	0.984	0.036	0.219
A38M6-1	6	25	0.984	0.040	0.219
A38M6-1.5	6	38	1.496	0.040	0.218
A38M8-1	8	25	0.984	0.042	0.250
A38M8-1.5	8	38	1.496	0.042	0.250
A38M10-1	10	25	0.984	0.046	0.281
A38M10-1.5	10	38	1.496	0.046	0.281
A38M12-1.5	12	38	1.496	0.050	0.297
A38M14-1.5	14	38	1.496	0.550	0.344

# TORX® POWER BITS



Puntas Torx®



Part No.	Torx Size	Length	
		mm	in
A3T6-2	T6	50	1.969
A3T7-2	T7	50	1.969
A3T7-2.75	T7	70	2.756
A3T7-3.5	T7	90	3.543
A3T7-6	T7	150	5.906
A3T8-2	T8	50	1.969
A3T8-2.75	T8	70	2.756
A3T8-3.5	T8	90	3.543
A3T8-6	T8	150	5.906
A3T9-2	T9	50	1.969
A3T9-2.75	T9	70	2.756
A3T9-3.5	T9	90	3.543
A3T9-6	T9	150	5.906
A3T10-2	T10	50	1.969
A3T10-2.75	T10	70	2.756
A3T10-3.5	T10	90	3.543
A3T10-6	T10	150	5.906

# TORX® POWER BITS


Puntas Torx®



Part No.	Torx Size	Length	
		mm	in
A3T15-2	T15	50	1.969
A3T15-2.75	T15	70	2.756
A3T15-3.5	T15	90	3.543
A3T15-6	T15	150	5.906
A3T20-2	T20	50	1.969
A3T20-2.75	T20	70	2.756
A3T20-3.5	T20	90	3.543
A3T20-6	T20	150	5.906
A3T25-2	T25	50	1.969
A3T25-2.75	T25	70	2.756
A3T25-3.5	T25	90	3.543
A3T25-6	T25	150	5.906
A3T27-2	T27	50	1.969
A3T27-2.75	T27	70	2.756
A3T27-3.5	T27	90	3.543
A3T27-6	T27	150	5.906
A3T30-2	T30	50	1.969
A3T30-2.75	T30	70	2.756
A3T30-3.5	T30	90	3.543
A3T30-6	T30	150	5.906
A3T40-2	T40	50	1.969
A3T40-2.75	T40	70	2.756
A3T40-3.5	T40	90	3.543
A3T40-6	T40	150	5.906

## TAMPER RESISTANT

Torx® (Extra Resistencia)



Part No.	Torx Size	Length	
		mm	in
A3T10-2TR	T10	50	1.969
A3T15-2TR	T15	50	1.969
A3T20-2TR	T20	50	1.969
A3T25-2TR	T25	50	1.969