


- Notes,
- Material, insert: PC UL-File Nr.: E101788(R)
 - Material contact: Fe
 - Material contact: CuNi Konstantan
 - Contact Surface: Silver, Gold
 - Strip length: Screw conection 7mm, Spring clamp conection 10mm, Crimp conection 7.5mm
 - Material: cover PBT UL-File Nr.: E69578
 - Packaging: 200 pieces

ITEM NO. POS.	REMARKS / BEMERKUNGEN	COLOR / FARBE	SURFACE/OBERFLÄCHE	MATERIAL	DESCRIPTION / BENENNUNG
10	M3x10	blau/blue	blank/even	V2A/stainless steel	Befestigungsschraube/fixing screw
9	M3x10	blau/blue	vernickelt/nickel plated	Stahl/steel	Befestigungsschraube/fixing screw
8			vergoldet/gold plated	Messing/brass	Kontaktstift Federklemme/contact spring clamp
7			versilbert/silver plated	Messing/brass	Kontaktstift Federklemme/contact pin
6			vergoldet/gold plated	Messing/brass	Kontaktstift Schraubanschluß/contact screw termination
5			versilbert/silber plated	Messing/brass	Kontaktstift Schraubanschluß/contact screw termination
4		lichtgrau/light grey			Deckel Federklemmversion/cover spring version
3		lichtgrau/light grey			Deckel Crimpversion/cover crimp version
2		lichtgrau/light grey			Deckel Schraubversion/cover screw version
1		lichtgrau/light grey			Stifteinsatz/pin insert



ORDERING TEXT / BESTELLTEXT

HE.10.Sti.SC-AU
HE.10.Sti.S.KM
HE.10.Sti.S-VA
HE.10.Sti.S-AU
HE.10.Sti.SC
HE.10.Sti.C
HE.10.Sti.S-T
HE.10.Sti.S

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIMENSIONS: DIMENSIONEN: mm. TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN. ISO 8015, ISO 2768 - mH - E, DIN 16901 - 140. ANGLES / WINKEL #, FINISH / OBERFLÄCHE / FARBE.

DWN Gräf 10.02.1999
CHK Schweiger 18.02.1999

AMP HTS Elektrotechnik
53819 Neunkirchen, Germany

Male insert
HE.10.STI.S/C

SIZE A3 CAGE CODE 00779 DRAWING NO. ZEICHNUNGS-NR. G-1103636 RESTRICTED TO NUR FUER

CUSTOMER DRAWING /KUNDENZEICHNUNG SCALE MASSSTAB 1:1 SHEET BLATT OF 1 VON 1 REV. A5