


AD9225GP SERIES



External Dimensions




Frame: Plastic(UL:94V-0)
 Impeller: Plastic(UL:94V-0)
 Bearing: Ball bearing
 Lead wire: UL1007AWG24
 Voltage Available: 24V

Specifications(Nominal)

*Noise is measured at the distance of one (1) meter from the axis of intake.
 Bearing type: ⊙=Ball ⊗=Sleeve ○=1B1S ●=Hypro bearing

| Frame size (mm) | Model No. | Bearing System Type | Rated Voltage (VDC) | Current (A) | Power (W) | Rated Speed (rpm) | Maximum AirFlow (CMM) | Maximum AirFlow (CFM) | Maximum Pressure (InAq) | Maximum Pressure (mmAq) | *Noise Level (dB/A) | Weight (g) |
|-----------------|----------------|---------------------|---------------------|-------------|-----------|-------------------|-----------------------|-----------------------|-------------------------|-------------------------|---------------------|------------|
| 92x92x25 | AD0924UB-A71GP | ⊙ | 24 | 0.18 | 4.32 | 3500 | 2.038 | 72.00 | 0.230 | 5.84 | 44.0 | 103.0 |
| | AD0924XB-A71GP | ⊙ | 24 | 0.24 | 4.80 | 4000 | 2.363 | 83.50 | 0.280 | 7.11 | 48.0 | |






Specifications subject to change without notice.



*Motor protective circuit and third lead wire functions

| | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|
| 0 | 1 | 2 | 3 | 4 | 6 | 7 | 8 | 9 | A | B |
| | ✓ | ✓ | ✓ | | | | | ✓ | | ✓ |

*Safety approvals

| | | | | |
|---|--|---|---|---|
|  |  |  |  |  |
| ✓ | ✓ | | ✓ | ✓ |