

selos



6 mm pitch



8 mm pitch



10 mm pitch

12 mm pitch

16 mm pitch

Type	Part no.	Std. pack	Type	Part no.	Std. pack	Type	Part no.	Std. pack
Marking strips, unmarked			Marking strips, unmarked			16 mm²/10 mm pitch		
9705 A/6/10	04.242.6053.0	25	9705 A/8/10	04.242.8053.0	25	marked for 5 blocks (every 2nd tag) *		
Marking strips, marked			Marking strips, marked			9705 A/5/10/5 B	04.842.5553.0	25
9705 A/6/9 B 1 - 9	04.842.5953.0	25	9705 A/8/9 B 1 - 9	04.842.7953.0	25	25 mm²/12 mm pitch		
9705 A/6/10 B*	04.842.6053.0	25	9705 A/8/10 B*	04.842.8053.0	25	marked for 5 blocks (every 2nd tag) *		
9705 A/6/10 B 1 - 10	04.846.0153.0	25	9705 A/8/10 B 1 - 10	04.848.0153.0	25	9705 A/6/10/5 B	04.842.6553.0	25
11 - 20	04.846.0253.0	25	11 - 20	04.848.0253.0	25	35 mm²/16 mm pitch		
21 - 30	04.846.0353.0	25	21 - 30	04.848.0353.0	25	marked for 5 blocks (every 2nd tag) *		
31 - 40	04.846.0453.0	25	31 - 40	04.848.0453.0	25	9705 A/8/10/5 B	04.842.8553.0	25
41 - 50	04.846.0553.0	25	41 - 50	04.848.0553.0	25	with enlarged marking area		
51 - 60	04.846.0653.0	25	51 - 60	04.848.0653.0	25	9705 AL/6/10 04.242.6353.0 25		
61 - 70	04.846.0753.0	25	61 - 70	04.848.0753.0	25	* Custom marking upon request		
71 - 80	04.846.0853.0	25	71 - 80	04.848.0853.0	25	*Custom marking upon request		
81 - 90	04.846.0953.0	25	81 - 90	04.848.0953.0	25	* indicate required marking with part no.		
91 - 100	04.846.1053.0	25	91 - 100	04.848.1053.0	25			
⊕ (10 x)	04.856.0053.0	25	⊕ (10 x)	04.858.0053.0	25			
⊖ (10 x)	04.856.0153.0	25	⊖ (10 x)	04.858.0153.0	25			
+ (10 x)	04.856.0253.0	25	+ (10 x)	04.858.0253.0	25			
- (10 x)	04.856.0353.0	25	- (10 x)	04.858.0353.0	25			
L1 (10 x)	04.856.0453.0	25	L1 (10 x)	04.858.0453.0	25			
L2 (10 x)	04.856.0553.0	25	L2 (10 x)	04.858.0553.0	25			
L3 (10 x)	04.856.0653.0	25	L3 (10 x)	04.858.0653.0	25			
PE (10 x)	04.856.0753.0	25	PE (10 x)	04.858.0753.0	25			
SL (10 x)	04.856.3153.0	25	SL (10 x)	04.858.3153.0	25			
N (10 x)	04.856.3253.0	25	N (10 x)	04.858.3253.0	25			
F1 (10 x)	04.856.0953.0	25	F1 (10 x)	04.858.0953.0	25			
F2 (10 x)	04.856.1053.0	25	F2 (10 x)	04.858.1053.0	25			
L1, L2, L3, N, PE (2 x)	04.856.0853.0	25	L1, L2, L3, N, PE (2 x)	04.858.0853.0	25			