






- NOTES:
- CARD SLOT ACCEPTS  $.050 \pm .004 / (1.27 \pm 0.10)$  MODULE THICKNESS. (MEASURED OVER P.C. PADS).
  - RECOMMENDED PCB THICKNESS:  $.062 \pm .007 / (1.57 \pm 0.18)$
  - REFER TO PRODUCT SPEC PS-71243-9999 FOR PERFORMANCE SPECIFICATIONS.
  - PRODUCT IS PACKAGED IN TRAYS.
  - RECOMMENDED MODULE LAYOUT SHALL BE PER JEDEC MO-161.
  - RECOMMENDED PLATING ON MODULE PADS: 30 MICROINCH/(0.76 MICROMETER) MINIMUM HARD GOLD (Au) OVER 79 MICROINCH/(2.0 MICROMETER) MINIMUM NICKEL (Ni).
  - SEE CHART FOR FORK/HOLE PRESENCE AND PLATING OPTION.
  - PRODUCT WILL HAVE DATE CODE STAMPED ON SIDE OF HOUSING.

MATERIALS:  
 HOUSING - GLASS FILLED LIQUID CRYSTAL POLYMER (LCP), UL 94V-0, COLOR: BLACK.  
 TERMINAL - PHOSPHOR BRONZE  
 LATCHES - GLASS FILLED HIGH TEMPERATURE NYLON, UL 94V-0, COLOR: IVORY.  
 FORKLOCKS - STAINLESS STEEL

PLATING:  
 CONTACT AREA: OPTION A: GOLD (Au) FLASH; THICKNESS=2-10 MICROINCH/(0.05-0.25 MICROMETER), OVER PALLADIUM-NICKEL (Pd-Ni); THICKNESS=30 MICROINCH/(0.76 MICROMETER) MINIMUM.  
 OPTION B: GOLD (Au) FLASH; THICKNESS=2-10 MICROINCH/(0.05-0.25 MICROMETER), OVER PALLADIUM-NICKEL (Pd-Ni); THICKNESS=20 MICROINCH/(0.51 MICROMETER) MINIMUM.

SOLDER TAILS: TIN (Sn); THICKNESS=150 MICROINCH/(3.81 MICROMETER) MINIMUM.  
 UNDERPLATE: NICKEL (Ni) OVER ENTIRE CONTACT.  
 FORKLOCKS: NONE

NOTE FOR LEAD FREE CONVERSION:  
 THE PRIMARY SHIPPING CARTON WILL BE LABELED "COMPLIANT TO ROHS DIRECTIVE 2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC". CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH LEAD.



E1	ADD LEAD FREE NOTE ECN# UCP2004-1132 DMORGAN 04/03/09		
E	CHG Sn-Pb THICKNESS ECN# UDI1999-0454 DMORGAN 99/08/09		
D3	REVISED PER ECR# U71162 97-4-15 LAURX		
D2	REVISED PER ECR# U70731 97-1-8 LAURX		
D1	REVISED PER ECR# U70361 96-10-9 LAURX		
D	REVISED PER ECR# U61133 96-9-26 LAURX		
C	REVISED PER ECR# U61450 5-28-96 JCL		
B	REVISED PER ECR# U61050 2-28-96 JCL		
A	INITIAL RELEASE PER ECR# U60675 12-6-95 JCL		
MFG, SH.	REV.	LTR.	REVISIONS
3	D3		
2	D3		
1	E1		

DIMENSIONS SHOWN (METRIC) INCH		UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm 1/2^\circ$	
3 PLAGE	$\pm .005$	---	---
2 PLAGE	---	$\pm 0.13$	---
1 PLAGE	---	$\pm 0.25$	---
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			
DRWG. BY: JCL	CHK'D. BY:	FILE NAME: S71736-01	SCALE: 2:1
APPRD. BY: DCB	SCALE: 2:1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	SIZE: CP
TITLE: $.050$ PITCH MULTI-KEY DIMM TALL LATCH RAM ASSEMBLY W/FORKLOCKS - SALES DWG		SHEET NO. 1 OF 3 DATE 12/06/95	
PART NO. 71736-0002		DRWG. NO. SDA-71736-0***	
SEE CHART		MFG. SH. REV. LTR. REVISIONS	

