



semi

C3 Semiconductor, LLC

Applications

- Phase Control
- Static Switching
- Light Dimming
- Motor Speed Control
- Kitchen Equipment
- Power Tools
- Solenoid Valve Controls:
 - Dishwashers
 - Washing Machines

- > Suitable for General Purpose AC Switching
- > 400A Surge
- > IGT = 50 mA
- > V_{DRM}/V_{RMM} 400, 600, 800 *and now 1200V*

CTA/CTB41

40Amp - 400/600/800/1200V - TRIAC

Absolute Maximum Ratings

	CONDITIONS	SYMBOL	RATING
RMS On-State Current (full sine wave)	$T_c = 80^\circ\text{C}$ $T_c = 95^\circ\text{C}$	TO-218 TO-218 Iso	$I_{T(RMS)}$ 40A
Non Repetitive Surge Peak On-State Current (Full Cycle, T_j Initial = 25°C)	$F = 50\text{ Hz}$ $F = 60\text{ Hz}$	I_{TSM}	400A 420A
I^2t Value for fusing	$t_p = 10\text{ ms}$	I^2t	880A ² s
Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$, $t_r < 100\text{ ns}$, $T_j = 125^\circ\text{C}$		di/dt	100A/ μs
Peak Gate Current @ $T_j = 125^\circ\text{C}$	$t_p = 20\text{ }\mu\text{s}$	I_{GM}	4A
Average Gate Power Dissipation @ $T_j = 125^\circ\text{C}$		$P_{G(AV)}$	1W
Storage Temperature Range		T_{stg}	-40 to +150°C
Operating Junction Temperature Range		T_j	-40 to +125°C
Isolation Voltage (CTA Series only)		V_{ISO}	2500 V_{RMS}

Electrical Characteristics

ALTERNISTOR/NO SNUBBER AND LOGIC LEVEL (3 Quadrants)			BW
$I_{GT}\text{ MAX @ }V_D = 12\text{ V, }R_L = 30\Omega$ NOTE 1	QI-II-III		50mA
$V_{GT}\text{ MAX @ }V_D = 12\text{ V, }R_L = 30\Omega$	QI-II-III		1.3V
$V_{GD}\text{ MIN @ }V_D = V_{DRM}, R_L = 3.3k\Omega$ $T_j = 125^\circ\text{C}$	QI-II-III		0.2V
$I_H\text{ MAX @ }I_T = 500\text{ mA}$ NOTE 2			75mA
$I_L\text{ MAX @ }I_G = 1.2\text{ }I_{GT}$	QI-III		70mA
$I_L\text{ MAX @ }I_G = 1.2\text{ }I_{GT}$	Q-II		100mA
$dv/dt\text{ MIN @ }V_D = 67\%V_{DRM}\text{ (gate open)}$ NOTE 2 $T_j = 125^\circ\text{C}$			1000V/ μs
$(di/dt)_c\text{ MIN without Snubber}$ NOTE 2 & 4 $T_j = 125^\circ\text{C}$			22A/ms
STANDARD (4 Quadrants)			B
$I_{GT}\text{ MAX @ }V_D = 12\text{ V, }R_L = 30\Omega$ NOTE 1	QI-II-III		50mA
$I_{GT}\text{ MAX @ }V_D = 12\text{ V, }R_L = 30\Omega$ NOTE 1	QIV		100mA
$V_{GT}\text{ MAX @ }V_D = 12\text{ V, }R_L = 30\Omega$	Q-All		1.3V
$V_{GD}\text{ MIN @ }V_D = V_{DRM}, R_L = 3.3k\Omega$ $T_j = 125^\circ\text{C}$	Q-All		0.2V
$I_H\text{ MAX @ }I_T = 100\text{ mA}$ NOTE 2			75mA
$I_L\text{ MAX @ }I_G = 1.2\text{ }I_{GT}$	QI-III-IV		75mA
$I_L\text{ MAX @ }I_G = 1.2\text{ }I_{GT}$	Q-II		160mA
$dv/dt\text{ MIN @ }V_D = 67\%V_{DRM}\text{ (gate open)}$ NOTE 2 $T_j = 125^\circ\text{C}$			500V/ μs
$(dv/dt)_c\text{ MIN @ } (di/dt)_c = 13.3\text{ A/ms}$ NOTE 2 $T_j = 125^\circ\text{C}$			10V/ μs



ISO9001 Certified

GENERAL NOTES

1. Minimum IGT is guaranteed at 5% of IGT max.
2. For both polarities of A2 referenced to A1
3. All parameters at 25 degrees C unless otherwise specified.
4. Commutating $dv/dt = 50\text{ V}/\mu\text{s}$, (exponential to 200 Vpk)



C3 Semiconductor, LLC

CTA/CTB41


40Amp - 400/600/800/1000V - TRIAC

Static Characteristics

V_T MAX @ $I_{TM} = 35$ A, $t_p = 380\mu s$ NOTE 2	$T_J = 25^\circ\text{C}$	1.55V
V_{TO} MAX @ Threshold Voltage NOTE 2	$T_J = 125^\circ\text{C}$	0.85V
R_d MAX @ Dynamic Resistance NOTE 2	$T_J = 125^\circ\text{C}$	16m Ω
I_{DRM} MAX @ $V_{DRM} = V_{RRM}$	$T_J = 25^\circ\text{C}$	5 μ A
I_{RRM} MAX @ $V_{DRM} = V_{RRM}$	$T_J = 125^\circ\text{C}$	3mA

Thermal Resistances

		SYMBOL	RATING
Junction to Case (AC)	TO-218	$R_{th(j-c)}$	0.8°C/W
Junction to Case (AC)	TO-218 Isolated	$R_{th(j-c)}$	1.1°C/W
Junction to Ambient	TO-218	$R_{th(j-a)}$	50°C/W
Junction to Ambient	TO-218 Isolated	$R_{th(j-a)}$	50°C/W



Dimensions

REF.	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	20.4		21.1	0.8		0.831
B		3.23			0.127	
C	14.35		15.60		0.565	
D	15.1		15.5	0.594		0.610
E	1.20		1.40	0.047		0.055
F	1.45		1.55	0.057		0.061
G	4.4		4.6	0.173		0.181
H	0.5		0.7	0.020		0.028
J	5.4		5.65	0.213		0.222
K	8.0		8.25	0.315		0.325
L	4.08		4.17	0.161		0.164
M	15.8		16.5	0.622		0.650
N	4.6		4.8	0.181		0.189
O	1.20		1.40	0.047		0.055
P	1.20		1.40	0.047		0.055
Q	2.7		2.9	0.106		0.114

Part Number Selection

Part Number	Voltage [Vpk]	I_T [mA]	Type	Package
CTA/CTB41-xxxB	400, 600, 800	50mA	Standard	TO-218
CTA/CTB41-xxxBW	400, 600, 800	50mA	Alternistor/No Snubber	TO-218

Part Number Designation





Fig. 1: Power dissipation versus RMS on-state current (full cycle).




Fig. 2: RMS on-state current versus case temperature (full cycle)




Fig. 3: On-state current versus on-state voltage (instantaneous values)




Fig. 4: Non-repetitive surge peak on-state current versus number of cycles.

© 2007 C3 Semiconductors, Specifications subject to change without notice.

For recommended applications and more information contact:
USA : Sales Support (888) 882-8689

Email : sales@c3semi.com WEB SITE : <http://www.C3semi.com>

Approvals

UL - Pending