# Agilent Probe Positioners

**Data Sheet** 

## A full suite of revolutionary probe positioners for quick and stable hands-free probing

- Easy-to-manipulate probe arms for hands-free browsing
- One or two articulated arms with stable high-mass base (N2784A and N2785A)
- Quick and stable XY positioning (N2786A)
- Stable 3D probe positioning for hard-to-reach XYZ access (N2787A)
- Compatible with most scope probes
- Applications: Hands-free probing for electronic components on PC boards





### Quick and stable XY browsing-N2784A and N2785A

The N2784A and N2785A probe positioners provide quick and stable X-Y positioning to PC boards and devices that require hands-free probing.

Unlike other probe positioners that require multiple adjustments to lock the probe holder into position, the N2784A and N2785A need only a "lift and drop" motion to position the probe in place. The weight stabilization technique used in the probe holder keeps constant pressure at the probing point so the probe tip stays in position even when the target board is bumped.

The N2784A and N2785A probe positioners are compatible with most Agilent scope probes, including InfiniiMax single-ended and differential browsers. They are also compatible with various probes manufactured by other vendors. The N2784A comes with a single positioning arm, while the N2785A comes with two positioning arms.




Figure 1. N2784A one-arm probe positioner




Figure 2. N2785A two-arm probe positioner



Figure 3. See a close-up view of the probing contact through the included 3X magnifying glass

### Low-cost two-legged positioner - N2786A

The N2786A is a low-cost, easy-touse XY axis probe holder for general purpose probing applications. The two-legged positioner is designed to be easy-to-use - the positioner itself has no controls to position it in place. This positioner has three different sized apertures into which various sized probes can be placed. All of Agilent's 2.5mm and 5mm passive probes such as N2870A-76A, 10073C, 10074C, N2862A, N2863A, 1165A etc. and most other passive probes in the market can be used with the N2786A positioner.

# Your ultimate 3D positioning solution - N2787A

The N2787A is a 3D probe positioner with a flexible, articulating arm that can be quickly positioned in a wide variety of configurations. At the same time it also allows fine-adjustment to the probe location to obtain stable contact. This universal probe holder fits most Agilent passive and active probes, including InfiniiMax single-ended or differential browsers.



Figure 4. N2786A two-leg probe positioner



Figure 5. N2787A 3D probe positioner

	N2786A two-legged positioner	N2787A 3D positioner	N2784A XY 1-arm positioner	N2785A XY 2-arm positioner
Probe compatibility	Agilent passive probes and single-ended active probes	Most of Agilent's probes, including InfiniiMax browsers		
Target applications	Quick XY positioning	3D (XYZ) positioning	Quick and s browsing	table XY

## **Compatible probes**

Description	N2784A/N2785A	N2786A	N2787A
InfiniiMax 1130A/1131A/1132A/1134A and 1168A/1169A active probe with single-ended or differential browser	$\checkmark$		
1156A/1157A/1158A active probe	$\checkmark$	$\checkmark$	$\checkmark$
1141A/1153A active probe	$\checkmark$		
1144A active probe			
N287xA passive probes			
116x passive probe			
N2782A/N2783A passive probe			
104xx passive probe			
Many other Agilent probes and oscilloscope probes from other vendors		$\checkmark$	$\checkmark$

## **Characteristics**


Product number	Specification	Weight
N2784A/N2785A	1 arm length x height: 320 mm x 158 mm	N2784A 850 g N2785A 1.25 kg
N2786A	height: 91.5 mm, width: 67 mm	51.5 g
N2787A	arm length: 200 mm, head length 45 mm, base diameter: 100 mm	1.52 kg


## **Ordering Information**

Product number	Description
N2784A	1-arm probe positioner
N2785A	2-arm probe positioner
N2786A	two leg positioner
N2787A	3D positioner

1. N2784A and N2785A include 3x magnifying glass, arm strap, cable tie, probe rest and manual. 2. N2786A includes manual.

3. N2787A includes probe head and manual. Probe is not included in the positioner.





## **Related Literature**

Publication title	Description	Publication number
Agilent oscilloscope probes and accessoties	Selection guide	5989-6162EN
Agilent 5000, 6000 and 7000 Series InfiniiVision oscilloscopes probes and accessories	Data sheet	5968-8153EN
Agilent Infiniium oscilloscope probes, accessories and options	Data sheet	5968-7141EN

## Agilent Email Updates

www.agilent.com/find/emailupdates Get the latest information on the products and applications you select.

# Agilent Direct

www.agilent.com/find/agilentdirect Quickly choose and use your test equipment solutions with confidence.

## Agilent Open 🔑

#### www.agilent.com/find/open

Agilent Open simplifies the process of connecting and programming test systems to help engineers design, validate and manufacture electronic products. Agilent offers open connectivity for a broad range of system-ready instruments, open industry software, PC-standard I/O and global support, which are combined to more easily integrate test system development.



#### www.lxistandard.org

LXI is the LAN-based successor to GPIB, providing faster, more efficient connectivity. Agilent is a founding member of the LXI consortium.

## **Remove all doubt**

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to

www.agilent.com/find/removealldoubt

Windows<sup>®</sup> is a U.S. registered trademark of Microsoft Corporation.

## www.agilent.com

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

#### www.agilent.com/find/contactus

### Americas

Singapore

Taiwan

Thailand

Canada	(877) 894-4414		
Latin America	305 269 7500		
United States	(800) 829-4444		
Asia Pacific			
Australia	1 800 629 485		
China	800 810 0189		
Hong Kong	800 938 693		
India	1 800 112 929		
Japan	0120 (421) 345		
Korea	080 769 0800		
Malaysia	1 800 888 848		

080 769 0800
1 800 888 848
1 800 375 8100
0800 047 866
1 800 226 008

### **Europe & Middle East**

-		
Austria	0820 87 44 11	
Belgium	32 (0) 2 404 93 40	
Denmark	45 70 13 15 15	
Finland	358 (0) 10 855 2100	
France	0825 010 700	
Germany	01805 24 6333	
Ireland	1890 924 204	
Israel	972-3-9288-504/544	
Italy	39 02 92 60 8484	
Netherlands	31 (0) 20 547 2111	
Spain	34 (91) 631 3300	
Sweden	0200-88 22 55	
Switzerland	0800 80 53 53	
United Kingdom	44 (0) 118 9276201	
Other European countries:		
www.agilent.com/find/contactus		
Revised: October 1, 2008		

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2009 Printed in USA, June 26, 2009 5989-9131EN

