



























Amp	Volt	Hz	IP Ident. colour + h	 Part No.	Plugs IEC/EN 60 309	 	EAN-No. 4015609...																														
gland entry																																					
																																					
16	400	50/60	6	219	  	10	000258																														
	110	50/60	4	219 504		198	013289																														
	230	50/60	9	219 509			013302																														
	440	60	11	219 511			013319																														
32	400	50/60	6	239	  	10	000326																														
	110	50/60	4	239 504		285	014446																														
	230	50/60	9	239 509			014477																														
	440	60	11	239 511			014491																														
63	400	50/60	6	269	  	5	000357																														
	110	50/60	4	269 504		668	015146																														
	230	50/60	9	269 509			015160																														
	440	60	11	269 511			015184																														
125	400	50/60	6	279	  	2	000371																														
	110	50/60	4	279 504		1473	015375																														
	230	50/60	9	279 509			015412																														
	440	60	11	279 511			015436																														
<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>m</th> <th>n</th> <th>u</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>132</td> <td>114</td> <td>37</td> <td>88</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>156</td> <td>135</td> <td>46</td> <td>103</td> <td>21</td> </tr> <tr> <td>63 A</td> <td>243</td> <td>195</td> <td>67</td> <td>110</td> <td>36</td> </tr> <tr> <td>125 A</td> <td>315</td> <td>258</td> <td>75,5</td> <td>130</td> <td>48</td> </tr> </tbody> </table>						Ampère	d	m	n	u	Pg	16 A	132	114	37	88	16	32 A	156	135	46	103	21	63 A	243	195	67	110	36	125 A	315	258	75,5	130	48		
Ampère	d	m	n	u	Pg																																
16 A	132	114	37	88	16																																
32 A	156	135	46	103	21																																
63 A	243	195	67	110	36																																
125 A	315	258	75,5	130	48																																
				control plug for phase sequence																																	
16	100 - 50/60 690			210 DF	  	10	007776																														
						173																															
32	100 - 50/60 690			230 DF	  	10	007820																														
						241																															
63	100 - 50/60 690			260 DF	  	5	007868																														
						685																															
<table border="1"> <thead> <tr> <th>Ampère</th> <th>d</th> <th>Øe</th> <th>f</th> <th>n</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>65</td> <td>65</td> <td>75</td> <td>37</td> </tr> <tr> <td>32 A</td> <td>72</td> <td>72</td> <td>88</td> <td>46</td> </tr> <tr> <td>63 A</td> <td>81</td> <td>81</td> <td>97</td> <td>67</td> </tr> </tbody> </table>						Ampère	d	Øe	f	n	16 A	65	65	75	37	32 A	72	72	88	46	63 A	81	81	97	67												
Ampère	d	Øe	f	n																																	
16 A	65	65	75	37																																	
32 A	72	72	88	46																																	
63 A	81	81	97	67																																	