97 Self-Adjusting Crimping Pliers for End Sleeves (ferrules)

with front loading, patented



square crimp



square crimp 0,08-10,0 +16 mm²

- ► for crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4
- ► for solder-free electrical connections
- front loading of the end sleeves (ferrules) into the tool
- ➤ simple handling as a result of self-adjustment to the size of the end sleeve (ferrule)
- with square crimping for optimum contact areas in the clamp connection
- repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- these tools have been set precisely (calibrated) in the factory
- optimum transmisson of force due to lever action for fatigue-reduced operation
- high operation comfort thanks to handy shape and low weight
- all stressed parts are made of special steel, oil-hardened and tempered

Special

The Self-Adjusting Crimping Plier for end sleeves (ferrules) with front and lateral loading allows secure and comfortable working even in confined areas.

Model 97 53 08:

- rimping from 0.08 10.0 mm² in one profile
- ► end sleeves (ferrules) up to 2.5 mm² can also be loaded parallely from the side

Model 97 53 09:

- rimping from 0.08 10.0 and 16.0 mm² in one profile
- with selector lever for setting the crimping area either to 0.08 10 mm² or 16 mm²

Article-No.	EAN-	Range of Application		Capacity		47	
	Code			•	Length		
	4003773-			mm²	AWG	mm	g
97 53 08	040187		end sleeves	0.08 - 10.0	28 - 7	190	475
			(ferrules)				
97 53 09	044550		end sleeves	0.08 - 10.0 +16	28 - 7 + 5	190	475
			(ferrules)				



Front loading of end sleeves (ferrules) e. g. in switchboards



97 53 08: Lateral loading of end sleeves (ferrules) e. g. in confined areas



Square crimping for optimum contact zones