



L1792A BARRIER STRIP

These rugged 12 way terminal blocks are moulded in polyester, and are not subject to accidental chipping.

The L1794A has two rows of screw terminations and it may be mounted direct onto a metal chassis as the contacts are fully shrouded by the moulding.

CURRENT RATING:	15A (using screw or soldered connections at 70°C maximum ambient) 5A (with fast on connections)
TEMPERATURE RANGE:	-55°C to +100°C (ambient)
VOLTAGE PROOF:	4 KV rms
CONTACT RESISTANCE:	≤3 milliohms
INSULATION RESISTANCE:	≥100 megohms
CREEPAGE RESISTANCE:	6.9mm (terminals to panel face)
TERMINATIONS:	2.8mm x 0.61mm for solderless snap on connections or solder.
MAXIMUM TORQUE (terminal screws):	0.7Nm
MATERIALS:	Moulding: polyester, black Terminals: brass, tinned Screws: steel, nickel plated 4 BA panhead
APPROVALS:	None

ORDERING REFERENCE: L1792A



BLP reserve the right to change without prior notice the information contained within this leaflet