

# MATERIAL SAFETY DATA SHEET



Date Issued: 03/30/2009  
 MSDS No: 1570-QT/G/54G  
 Date Revised: 04/17/2009  
 Revision No: 1

## Eco-Stencil

### 1. PRODUCT AND COMPANY IDENTIFICATION

**PRODUCT NAME:** Eco-Stencil  
**PRODUCT DESCRIPTION:** SMT Stencil Cleaner  
**PRODUCT CODE:** 1570-QT/G/54G

#### MANUFACTURER

Techspray, L.P.  
 1001 N.W. 1st Street  
 P.O. Box 949  
 Amarillo TX 79107

**Emergency Contact:** Chemtrec  
**Product Stewardship:** 1-800-858-4043  
**Service Number:** 1-800-858-4043

#### 24 HR. EMERGENCY TELEPHONE NUMBERS

**CHEMTREC (US Transportation) :**(800) 424 - 9300  
**CANUTEC (Canadian Transportation) :**(613) 996 - 6666  
**Emergency Phone :**(800) 858 - 4043

### 2. HAZARDS IDENTIFICATION

#### HAZARD DESIGNATION

"Xi" - Irritant  
 R36/37/38 - Irritating to eyes, respiratory system and skin.  
 "Xn" - Harmful  
 R22 - Harmful if swallowed.

#### EMERGENCY OVERVIEW

**IMMEDIATE CONCERNS:** Harmful if swallowed. Aspiration hazard.

#### POTENTIAL HEALTH EFFECTS

**EYES:** Causes eye irritation.  
**SKIN:** May cause skin irritation.  
**SKIN ABSORPTION:** Skin absorption can occur.  
**INGESTION:** Harmful if swallowed.  
**INHALATION:** Prolonged or excessive inhalation may cause respiratory tract irritation.

#### SIGNS AND SYMPTOMS OF OVEREXPOSURE

**EYES:** Liquid splashed in the eye may cause redness, irritation and conjunctivitis.  
**SKIN:** Prolonged or exposure may cause skin irritation.  
**SKIN ABSORPTION:** Glycol ether ingredients may be absorbed through skin.  
**INGESTION:** For large amounts; abdominal pain, nausea and vomiting.  
**INHALATION:** Inhalation may cause respiratory tract irritation.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

# MATERIAL SAFETY DATA SHEET



Date Issued: 03/30/2009  
 MSDS No: 1570-QT/G/54G  
 Date Revised: 04/17/2009  
 Revision No: 1

## Eco-Stencil

Chemical Name	Wt.%	CAS	EINECS
Water	85 - 95	7732-18-5	231-791-2
2-propanol-1-butoxy	1 - 5	5131-66-8	225-878-4
Alcohols, C6-C12, ethoxylated propoxylated	< 2	68937-66-6	
Includes other components in less than reportable amounts	< 3		

### 4. FIRST AID MEASURES

**EYES:** Immediately flush eyes with plenty of water for at least 15 minutes. Get immediate medical attention.

**SKIN:** Immediately wash skin with soap and plenty of water. Remove contaminated clothing. Get medical attention if symptoms occur. Wash clothing before reuse.

**INGESTION:** Aspiration hazard. If swallowed, vomiting may occur spontaneously, but do not induce. If vomiting occurs, keep head below hips to prevent aspiration into lungs. Call a physician immediately.

**INHALATION:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.

### 5. FIRE FIGHTING MEASURES

**FLASHPOINT AND METHOD:** 96°C (205°F) TAG CC

**Notes:** This material is an aqueous solution and has a flash point above 200 degrees F. It will not sustain combustion.

**HAZARDOUS COMBUSTION PRODUCTS:** Combustion generates smoke and fumes of oxides of carbon/nitrogen.

**FIRE FIGHTING EQUIPMENT:** As in any fire, wear self-contained breathing apparatus pressure-demand, (MSHA/NIOSH approved or equivalent) and full protective gear.

### 6. ACCIDENTAL RELEASE MEASURES

**SMALL SPILL:** Avoid runoff into storm sewers and ditches which lead to waterways.

**GENERAL PROCEDURES:** Dike area to contain spill. Take precautions as necessary to prevent contamination of ground and surface waters. Recover spilled material on adsorbent, such as sawdust or vermiculite, and sweep into closed containers for disposal. After all visible traces, including vapors, have been removed thoroughly wet vacuum the area. Do not flush to sewer. If area of spill is porous, remove as much contaminated earth, gravel, etc. as necessary and place in closed containers for disposal.

### 7. HANDLING AND STORAGE

**GENERAL PROCEDURES:** Wash thoroughly after handling. Use only in a well ventilated area. Follow all MSDS/label precautions even after container is emptied because they may retain product residues. Store in a cool dry place.

# MATERIAL SAFETY DATA SHEET



Date Issued: 03/30/2009  
 MSDS No: 1570-QT/G/54G  
 Date Revised: 04/17/2009  
 Revision No: 1

## Eco-Stencil

### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

#### EXPOSURE GUIDELINES

OSHA HAZARDOUS COMPONENTS (29 CFR1910.1200)					
		EXPOSURE LIMITS			
		OSHA PEL		ACGIH TLV	
Chemical Name		ppm	mg/m <sup>3</sup>	ppm	mg/m <sup>3</sup>
2-propanol-1-butoxy	TWA	NE [1]	[1]	NE [1]	[1]
	STEL	NE [1]	[1]	NE [1]	[1]
<b>OSHA TABLE COMMENTS:</b>					
1. NOT ESTABLISHED					

**ENGINEERING CONTROLS:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits.

#### PERSONAL PROTECTIVE EQUIPMENT

**EYES AND FACE:** For normal conditions, wear safety glasses. Where there is reasonable probability of liquid contact, wear splash-proof goggles.

**SKIN:** Gloves of the following materials may provide protection against permeation: Viton, solvex, Buna, Butyl, and Neoprene.

**WORK HYGIENIC PRACTICES:** Avoid contact with eyes. Avoid fume inhalation. Limit skin contact.

### 9. PHYSICAL AND CHEMICAL PROPERTIES

**PHYSICAL STATE:** Liquid

**ODOR:** Faint ethereal odor

**APPEARANCE:** Clear, mobile liquid.

**pH:** 5 to 6

**PERCENT VOLATILE:** 96.9 at 104°C

**VAPOR PRESSURE:** < 0.01 mmHg@20C (VOC Composite Vapor Pressure)

**BOILING POINT:** ~ 100°C (212°F)

**FLASHPOINT AND METHOD:** 96°C (205°F) TAG CC

**Notes:** This material is an aqueous solution and has a flash point above 200 degrees F. It will not sustain combustion.

**SOLUBILITY IN WATER:** Fully miscible

**DENSITY:** 0.99 at 25°C (77°F)

**(VOC):** 2.670 % by weight

# MATERIAL SAFETY DATA SHEET



Date Issued: 03/30/2009  
MSDS No: 1570-QT/G/54G  
Date Revised: 04/17/2009  
Revision No: 1

## Eco-Stencil

Notes: 26.5 g/l

### 10. STABILITY AND REACTIVITY

**STABILITY:** Stable.

**POLYMERIZATION:** Will not occur.

**CONDITIONS TO AVOID:** Heat, flames, ignition sources, and incompatibles.

**INCOMPATIBLE MATERIALS:** Strong acids and alkalis, reactive metals and strong oxidizing agents.

### 11. TOXICOLOGICAL INFORMATION

#### ACUTE

**EYES:** Moderately to severely irritating

**DERMAL LD<sub>50</sub>:** Mildly to moderately irritating.

**SKIN ABSORPTION:** Skin absorption may occur with glycol ethers. No further information available.

**INHALATION LC<sub>50</sub>:** Not Established

**EYE EFFECTS:** Mixture is a moderate eye irritant.

**SKIN EFFECTS:** Causes irritation to skin.

#### CARCINOGENICITY

Chemical Name	NTP Status	IARC Status	OSHA Status
2-propanol-1-butoxy	NOT LISTED	NOT LISTED	NOT LISTED

**IARC:** NOT listed

**NTP:** NOT listed

**OSHA:** NOT listed

### 12. ECOLOGICAL INFORMATION

**ENVIRONMENTAL DATA:** There is limited information available on the environmental fate and effects of this material. The primary environmental concern for release is the impact on aquatic and terrestrial species. Due care should be taken to avoid the accidental release of this material into the environment.

### 13. DISPOSAL CONSIDERATIONS

**DISPOSAL METHOD:** Federal, State, and Local laws governing disposal of materials can differ. Ensure compliance with proper authorities before disposal.

### 14. TRANSPORT INFORMATION

# MATERIAL SAFETY DATA SHEET



Date Issued: 03/30/2009  
MSDS No: 1570-QT/G/54G  
Date Revised: 04/17/2009  
Revision No: 1

## Eco-Stencil

### DOT (DEPARTMENT OF TRANSPORTATION)

**PROPER SHIPPING NAME:** Not regulated

**UN/NA NUMBER:** NA

**PACKING GROUP:** NA

### ROAD AND RAIL (ADR/RID)

**PROPER SHIPPING NAME:** Not regulated

### AIR (ICAO/IATA)

**SHIPPING NAME:** Not regulated

### VESSEL (IMO/IMDG)

**SHIPPING NAME:** Not regulated

## 15. REGULATORY INFORMATION

### UNITED STATES

#### SARA TITLE III (SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT)

**311/312 HAZARD CATEGORIES:** ACUTE

**FIRE:** No **PRESSURE GENERATING:** No **REACTIVITY:** No **ACUTE:** Yes **CHRONIC:** No

**313 REPORTABLE INGREDIENTS:** None

#### CERCLA (COMPREHENSIVE RESPONSE, COMPENSATION, AND LIABILITY ACT)

**CERCLA REGULATORY:** Glycol ethers, RQ = 1.

#### TSCA (TOXIC SUBSTANCE CONTROL ACT)

Chemical Name	CAS
Water	7732-18-5

### CLEAN AIR ACT

**40 CFR PART 68---RISK MANAGEMENT FOR CHEMICAL ACCIDENT RELEASE PREVENTION:** NOT listed

### OCCUPATIONAL SAFETY AND HEALTH ADMINISTRATION (OSHA)

**29 CFR1910.119---PROCESS SAFETY MANAGEMENT OF HIGHLY HAZARDOUS**

**CHEMICALS:** None of the chemicals in this product are considered highly hazardous by OSHA.

**CALIFORNIA PROPOSITION 65:** This product contains no listed substances known to the State of California to cause cancer, birth defects or other reproductive harm, at levels which would require a warning under the statute.

### CANADA

**WHMIS CLASS:** Class D2B - Toxic Materials

### EUROPEAN COMMUNITY

