


REVISIONS			
REV	DESCRIPTION	DATE	NAME
A	Initial Release.	05-07-09	AMH
B	Updated temp spec and labeling	08-17-09	AMH




Dawar Tech: PL8_7.0W-00001R.B
 XXXXXX XXXXX XXXXXXXXXXXXX

Pin#	Assignment
Pin1	Right excite
Pin2	Right sense
Pin3	Top sense
Pin4	Top excite
Pin5	Left excite
Pin6	Left sense
Pin7	Bottom sense
Pin8	Bottom excite

NOTES:

- 1.Operation Temperature:-20°C~+60°C
Storage Temperature:-20°C~+70°C
- 2.Life Time :>5,000,000 times.
- 3.Linearity : ≤1.5%.
- 4.ITO Film:Anti-glare & Hardng Coating Anti-Newton Ring
Sheet Resistance: 400±100 Ohm/square;
ITO Film: Clear- Anti-Newton Ring
Sheet Resistanc:400±100 Ohm/square
- 5.Tail Type :Gold plated FPC
- 6.All Tolerance Without Marked:±0.3
- 7.All Materials and Components must be RoHS compliant
- 8.No Material is allowed to be larger than the glass size



 1016 North Lincoln Avenue - Pittsburgh, PA 15233-2302 1.800.386.1904 - 412.322.9900 - Fax: 412.322.9956 e-mail: sales@sawar.com - www.dawar.com	CUSTOMER NAME	UNIT	DAWAR P/N	REV
	Standard product offering	mm	PL8_7.0W-00001	B
	CUSTOMER P/N	REV	DRAWN BY	DATE
			Jason Liao	08-17-09
	DESCRIPTION	SHEET	MANUFACTURING NO.	REV
	7.0"W 8-Wire Resistive Touch Screen	1 OF 1		

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.