


- **E2A-M12KS04-WP-B1 2M**

Lead Contents

E2A-M12KS04-WP-B1 2M



*3D-CAD CG View

- [Inquiry of E2A-M12KS04-WP-B1 2M](#)

Related Contents

Products links

Find OMRON IA Products in your country

Quick links to 'E2A' page in your country / territory.

- [Europe](#)
 - [Austria](#)
 - [Belgium](#)
 - [Czech Republic](#)
 - [Denmark](#)
 - [Finland](#)

- Japan / Korea
 - [Japan](#) 
 - [Korea](#) 
- Americas
 - [Argentina](#) 
 - [Brazil](#) 
 - [Canada](#) 
 - [Mexico](#) 
 - [United States](#) 
 - [United States \[Safety\]](#) 

Get more support via Products links, such as manuals and CAD files.

Related Contents

Similar items

- [E2A-M12KS04-WP-B1 5M](#)
- [E2A-M12KS04-WP-B2 2M](#)
- [E2A-M12KS04-WP-B2 5M](#)
- [Item index of E2A](#)

Primary Contents

- [Ratings / Performance](#)
- [Dimensions](#)
- [Output circuit diagram](#)
- [Timing chart](#)
- [Sensing range](#)
- [Sensing distance vs. size and material of sensing object](#)
- [Mutual interference](#)
- [Effects of surrounding metals](#)

Shield	Shielded
Cylinder type sensing head size	M12

Sensing method	Inductive type
Sensing distance	4 mm -10% to +10%
Setting distance	0 to 3.2 mm
Differential distance	10% Max. of sensing distance
Sensing object	Ferrous metal (Sensitivity lowers with non-ferrous metals.)
Standard sensing object	Iron 12*12*1mm
Response frequency (Average)	DC: 1 kHz
Power supply voltage	12 to 24 VDC (ripple(p-p) :10% Max.)
Operating voltage range	10 to 32 VDC
Current consumption	10 mA Max.
Control output (Output type)	PNP open collector output
Control output (Switching capacity)	0 to 200 mA
Control output (Residual voltage)	(DC) 2 V Max. (under load current with cable length of 2m)
Indicator	Operation indicator(yellow)
Operation mode	NO
Protective circuit	Surge suppressor Output short-cut protection Output reverse polarity protection Power supply reverse polarity protection
Standard or Different frequency	Standard
Ambient temperature	Operating: -40 to 70 CEL Storage: -40 to 85 CEL (with no icing or condensation)
Ambient humidity	Operating: 35 to 95 %RH Storage: 35 to 95 %RH (with no condensation)
Temperature influence	+/-10% Max. of sensing distance in temperature range of -25 to +70CEL +/-15% Max. of sensing distance in temperature range of -40 to +70CEL (As the basis for sensing distance of 23CEL)
Voltage influence	+/-1% Max. of sensing distance in rated voltage range +/-15%. (As the basis for sensing distance at standard power voltage)
Insulation resistance	50 M OHM Min. at 500VDC between charged parts and the case
Dielectric strength	1000 VAC 50/60 Hz for 1 minute between charged parts and the case
Vibration resistance	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions
Shock resistance	1000m/s ² for 10 times each in X, Y, and Z directions
Degree of protection	IEC60529: IP67
Applicable standard (EC Directive (Low Voltage Directive))	EN60947-1 EN60947-5-2
Applicable standard (EC Directive (EMC Directive))	EMI: EN60947-5-2 Emission Enclosure: CISPR11 Group 1 classA EMS: EN60947-5-2 Immunity ESD: IEC61000-4-2 Immunity RF-interference: IEC61000-4-3 Immunity Conducted Disturbance: IEC61000-4-6 Immunity Burst: IEC61000-4-4 CE marking: Equipped
Applicable standard (CCC mark)	Not equipped
Connection method	Pre-wired models (Cable length: 2 m)
Weight (Packed state)	approx. 85 g
Material (case)	Brass nickel plating
Material (sensing surface)	PBT
Material (clamping nuts)	Brass nickel plating
Material (toothed washer)	Iron zinc plating