

ADK Precision Balances



“The Affordable Choice”

ADK Precision Balances


“The Affordable Choice”

The ADK with its large weighing pan and cast aluminium base is ideal for heavy capacity weighing.

- Force restoration mechanism
- Robust construction with heavy duty casing
- Stainless steel weighing pan
- Full range tare
- Push-button calibration
- Vacuum fluorescent display
- RS-232 interface
- Simple key operation
- Anti-shock protection
- Below pan weighing facility

SPECIFICATIONS

Model	ADK 10	ADK 20
Maximum capacity	10kg	20kg
Readability	0.1g	0.1g
Resolution	0.1g	0.1g
Tare range	Full	Full
Repeatability	0.1g	0.1g
Linearity (±)	0.2g	0.2g
Typical stabilisation time	3 - 5 sec	3 - 5 sec
Units of measure	g	
Interface	RS232 output	
Operating temperature	5°C to 30°C	
Power supply	Power cord 240V or 115V option via switch on unit	
Calibration	Automatic external	
Display	LED	
Pan size	300x340mm / 11.8x13.4"	
Overall dimensions (wxdxh)	314x460x164 mm / 12.4x18.1 x6.5"	
Gross weight	23kg / 51lb	
Applications	Heavy capacity weighing	
Functions	Weigh Only	
Other features	Below balance weighing with optional hook	



Optional Accessories

- Anti-vibration table
- Below balance weighing hanger
- Standard printer
- Statistics printer



Adam Equipment have offices in the UK, USA and South Africa

www.adamequipment.com