

# **Features**

## 32.21-x000

## 32.21-x300

### Printed circuit mount 6 A relay


- 1 Pole changeover contacts or 1 Pole normally open contact
- Subminiature, low profile package
- Sensitive DC coil 200 mW
- Wash tight: RT III
- Cadmium Free contact material option





- 1 CO (SPDT), 6 A
- Low coil power
- PCB mount





- 1 NO (SPST-NO), 6 A
- Low coil power
- PCB mount











Copper	side	view
--------	------	------


Copper side view

		Copper side view	Copper side view
Contact specification			
Contact configuration		1 CO (SPDT)	1 NO (SPST-NO)
Rated current/Maximum p	eak current A	6/15	6/15
Rated voltage/Maximum sv	vitching voltage V AC	250/400	250/400
Rated load AC1	VA	1,500	1,500
Rated load AC15 (230 V	AC) VA	250	250
Single phase motor rating	(230 V AC) kW	0.185	0.185
Breaking capacity DC1: 3	0/110/220 V A	3/0.35/0.2	3/0.35/0.2
Minimum switching load	mW (V/mA)	500 (10/5)	500 (10/5)
Standard contact material		AgCdO	AgCdO
Coil specification			
Nominal voltage $(U_N)$	V AC (50/60 Hz)	<del>-</del>	_
	V DC	5 - 12 - 24 - 48	5 - 12 - 24 - 48
Rated power AC/DC	VA (50 Hz)/W	<b>—</b> /0.2	<b>—/0.2</b>
Operating range	AC	<del>-</del>	_
	DC	(0.781.5)U <sub>N</sub>	(0.781.5)U <sub>N</sub>
Holding voltage	AC/DC	—/0.4 U <sub>N</sub>	—/0.4 U <sub>N</sub>
Must drop-out voltage	AC/DC	/0.1 U <sub>N</sub>	—/0.1 U <sub>N</sub>
Technical data			
Mechanical life AC/DC	cycles	—/20 · 10 <sup>6</sup>	—/20 · 10 <sup>6</sup>
Electrical life at rated load	AC1 cycles	100 · 10³	100 · 10³
Operate/release time	ms	6/4	6/2
Insulation between coil and contacts (1.2/50 µs) kV		5	5
Dielectric strength between	open contacts V AC	1,000	1,000
Ambient temperature rang	e °C	-40+85	-40+85
Environmental protection		RT III	RT III
Approvals (according to type)		<b>(R</b> ) • <b>3</b>	US VDE



# **Ordering information**

Example: 32 series PCB, 1 NO (SPDT-NO) - 6 A contacts, 24 V sensitive DC coil.



Selecting features and options: only combinations in the same row are possible.

Preferred selections for best avaliability are shown in **bold**.

ı	Туре	Coil version	Α	В	С	D
ı	32.21	sens. DC	<b>2</b> - 4	0 - 3	0	0


## **Technical data**

Insulation according to EN 61810	-1:2004			
Nominal voltage of supply system	v AC	230/400		
Rated insulation voltage	V AC	250		
Pollution degree		2		
Insulation between coil and conta	ct set			
Type of insulation		Basic		
Overvoltage category		III		
Rated impulse voltage	kV (1.2/50 μs)	4		
Dielectric strength	V AC	4,000		
Insulation between open contacts				
Type of disconnection		Micro-disconnection		
Dielectric strength	V AC/kV (1.2/50 μs)	1,000/1.5		
Conducted disturbance immunity				
Burst (550)ns, 5 kHz, on A1 - A	42	EN 61000-4-4	level 4 (4 kV)	
Surge (1.2/50 µs) on A1 - A2 (d	ifferential mode)	EN 61000-4-5	level 3 (2 kV)	
Other data				
Bounce time: NO/NC	ms	2/10 (changeover)	2/— (normally open)	
Vibration resistance (555)Hz: N	NO/NC g	10/10 (changeover)	10/— (normally open)	
Shock resistance	g	20		
Power lost to the environment	without contact current W	0.2		
	with rated current W	0.5		
Recommended distance between	relays mounted on PCB mm	≥ 5		




# **Contact specification**

#### F 32 - Electrical life (AC) v contact current



#### H 32 - Maximum DC1 breaking capacity




- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of  $\geq 100 \cdot 10^3$  can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
  Note: the release time for the load will be increased.

# **Coil specifications**

#### DC coil data - 0.2 W sensitive

Nominal	Coil	Operating range		Resistance	Rated coil
voltage	code				consumption
U <sub>N</sub>		$U_{min}$	U <sub>max</sub>	R	I at U <sub>N</sub>
V		V	V	Ω	mA
5	<b>7</b> .005	3.9	7.5	125	40
12	<b>7</b> .012	9.4	18	720	16
24	<b>7</b> .024	18.7	36	2,880	8.3
48	<b>7</b> .048	37.4	72	11,520	4

## R 32 - DC coil operating range v ambient temperature



- 1 Max. permitted coil voltage.
- 2 Min. pick-up voltage with coil at ambient temperature.