3182VR





Specifications:

Core-earth/core-core voltage rating : 300/500.

Maximum operating temperature : 60°C.

Reel length : 100m.

Conductor material : Plain copper.

Primary insulation material : Rubber.

Secondary insulation material : Rubber.

Secondary insulation colour : Black.

Specification Table

Primary Insulation Colour	Cable Type	Current Rating (A)	Number of Cores	Conductor Area CSA (mm2)	External Diameter (mm)	Conductor Make-up	Part Number
Blue, Brown	3182VR/TRS	6	2	0.75	6.3	24/0.20	3182VR 0.75 FLEX
		10		1.00	7.7	32/0.20	3182VR 1.00 FLEX
		15		1.50	9.4	30/0.25	3182VR 1.50 FLEX
Blue, Brown, Green/Yellow	3183VR/TRS	6	3	0.75	7.7	24/0.20	3183VR 0.75 FLEX
		10		1.00	8.1	32/0.20	3183VR 1.00 FLEX
		15		1.50	9.8	30/0.25	3183VR 1.50 FLEX

Dimensions: Millimetres

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-Power is the registered trademark of the Group. © Premier Farneli plc 2010.



