
ABMT-801-RC Specification Sheet





Feature:

• All data at 25°C unless otherwise specified.



Dimensions : Millimetres

Specifications:

General tolerance	: ±
Housing material	: L(
Rated voltage	: 3.
Operating voltage	: 2.
Maximum rated current at rated voltage	: 10
Sound output at 10cm, at rated voltage	: M
Resonant frequency at rated voltage	: 40
Operating temperature	: -3
Storage temperature	: -4
Weight	: 0.

```
: ± 0.2 (if not specified).

: LCP.

: 3.0 Vp-p.

: 2.0 - 4.0 Vp-p.

ge : 100mA.

ge : MIN 78 (typical 82).

: 4000.

: -30 to +70°C.

: -40 to +85°C.
```


: 0.3(g).





ABMT-801-RC Specification Sheet





Part Number Table

Description	Part Number
Audio Transducer, Emech, SMT, 5 x 5mm	ABMT-801-RC



Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheets previously for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-SIGNAL is the registered trademark of the Group. © Premier Farnell pic 2010.

Page 2

http://www.farnell.com http://www.newark.com http://www.cpc.co.uk

