



Scotch® Linerless Rubber Splicing Tape 130C

Data Sheet

Product Description

Scotch® Linerless Rubber Splicing Tape 130C is a highly conformable, linerless, ethylene rubber (EPR), high-voltage insulating tape, formulated to provide excellent thermal dissipation of splice heat. The tape is designed for use in splicing and terminating wires and cables. Rated up to 90°C continuous operating temperatures and short-term 130°C overload service. The tape has excellent physical and electrical properties, which provide immediate moisture seals and void-free build-ups. This product can be used for low and high-voltage (through 69 kV) applications.

- Linerless, self-bonding, primary insulating tape rated through 69 kV.
- High thermal conductivity.
- Ethylene propylene base.
- Excellent physical and electrical properties.
- Designed to insulate splices and terminate cables whose overload temperatures can reach 130°C.
- Physical and electrical properties unaffected by degree of stretch
- Compatible with common, solid dielectric cable insulation
- Uniform tape unwind from roll
- Small roll size (O.D.)
- Five-year shelf life
- Stable over wide application temperature range
- Weather resistant

Applications

- Primary insulation for splicing all types of solid dielectric insulated cables through 69 kV
- Primary insulation for building stress cones on all types of solid dielectric insulated cables up to 35 kV
- Jacketing (secondary insulation) on high-voltage splices and terminations
- Moisture-sealing electrical connections
- Bus bar insulation

- End-sealing high-voltage cables
- Motor leads
- Jacket repairs

Typical Data/Physical Properties

Physical Properties

Test Method	Typical Value*
Color	Black
Thickness (ASTM-D-4325)	30 mils (0,762 mm)
Tensile Strength (ASTM-D-4325)	250 psi (1,72 MPa)
Ultimate Elongation (ASTM-D-4325)	850%
Operating Temperature (ASTM-D-4388)	90°C (194°F)
Emergency Overload (ASTM-D-4388)	130°C (266°F)
Thermal Conductivity (23°C) (ASTM-C-518)	0.3 W/m°C
Ozone Resistance (ASTM-D-4388)	Pass
Heat Resistance (ASTM-D-4388)	Pass
UV Resistance (ASTM-D-4388)	Pass

Physical Properties

Test Method	Typical Value*
Dielectric Strength (ASTM-D-4325)	
Original	750 V/mil (29,5 MV/m)
24 hrs. in H ₂ O	750 V/mil (29,5 MV/m)
96 hrs. @ 23°C 96% RH	730V/mil (28,7 MV/m)

Volume Resistivity (ASTM-D-4325)

Original	>10 ¹⁵ ohm-cm
Aged 96 hrs. @ 23°C 96% RH	>10 ¹⁴ ohm-cm

Dielectric Constant (ASTM-D-4325)

1200 volts @ 60 Hz	
23°C	3.5
90°C	3.6

Dissipation Factor (ASTM-D-4325)

1200 volts @ 60 Hz	
23°C	0.70%
90°C	3.00%

** All values are averages and are not intended for specification purposes.*

Specification

Product

The high-voltage corona resistant tape must be supplied without a liner, be based on ethylene propylene rubber, and be capable of emergency operating cable temperature of 130°C. The tape must be capable of being applied in either stretched or unstretched conditions without resulting in loss of either physical or electrical properties. The tape must not split, crack, slip, or flag when exposed to various environments (indoor or outdoor). The tape must be compatible with all synthetic cable insulations and have a shelf life of five years.

Engineering/Architectural Specification

Splicing and terminating solid dielectric cable shall be done in accordance with drawings engineered by the splice material manufacturer. All splices and terminations shall be insulated using Scotch® Electrical Tape 130C.

3M and Scotch are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of one (1) year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electrical Markets Division

6801 River Place Blvd.
Austin, TX 78726-9000
800-626-8381
Fax 800-828-9329
www.3M.com/electrical



Recycled paper
40% Pre-consumer waste paper
10% Post-consumer waste paper

Litho in USA
© 3M 2005 78-8125-9449-3-B

Installation Technique

This tape should be applied in successive half-lapped level wound layers until desired build-up is reached. It should be applied like any rubber tape; that is, the side of the tape wrapped inside the roll should be applied outside on the splice (tacky side up). This will help prevent the roll from getting progressively further away from the work area.

To eliminate voids in critical areas, highly elongate 130C tape. Stretch tape in critical areas just short of the breaking point; doing so will not alter its physical or electrical properties. In less critical areas, less elongation may be used. The tape should be stretched to a minimum of 3/4 its original width. Always attempt to half-lap to produce a uniform buildup. When using 130C tape for splicing cable above 15 kV, always highly elongate the tape throughout the entire splice. Techniques for proper usage of 130C tape are contained in standard and special prints available through the "3M System for Splicing and Terminating" program. These are available through the local 3M Electrical Products Division representative.

Shelf Life

The 130C tape has a 5-year shelf life (from date of manufacture) when stored under the following recommended storage conditions. Store behind present stock in a clean dry place at a temperature of 70°F (21°C) and 40% to 50% relative humidity. Good stock rotation is recommended.

Availability

The 130C tape is available from your electrical distributor in the following roll sizes.

- 3/4 in. by 30 ft. (19 mm x 9,1 m)
- 1 in. by 30 ft. (25,4 mm x 9,1 m)
- 1 1/2 in. by 30 ft. (38 mm x 9,1 m)
- 2 in. by 30 ft. (50,8 mm x 9,1 m)