
Solid State Relay G3R-I/O

Compact SSRs for I/O Interface with High Dielectric Strength Requirements

- High-speed models with optimum input ratings for a variety of sensors are available.
- Input Modules and Output Modules that have the same footprint as the G2R.
- Using a coupler approved by VDE 0884 and assuring an I/O dielectric strength of 4 kV.
- Incorporating an easy-to-see monitoring indicator.
- Approved by UL, CSA, and TÜV.
- Can be used with P2RF-05E socket for use on 35 mm DIN track.



Ordering Information

To Order: Select the part number and add the desired coil voltage rating, (e.g., G3R-IAZR1SN-DC5)

■ Input Module

Isolation	Indicator	Response speed	Logi	c level	Rated input	Model
			Supply voltage	Supply current	voltage	
Photocoupler	Yes	_	4 to 32 VDC	0.1 to 100 mA	100 to 240 VAC	G3R-IAZR1SN
		High-speed			5 VDC	G3R-IDZR1SN
		(1 kHz)			12 to 24 VDC	
		Low-speed			5 VDC	G3R-IDZR1SN-1
		(10 Hz)			12 to 24 VDC	

■ Output Module

Isolation	Indicator	Zero cross function	Rated output load	Rated input	Model
Phototriac	Yes	Yes	2 A at 100 to 240 VAC	5 to 24 VDC	G3R-OA202SZN
		No			G3R-OA202SLN
Photocoupler		_	2 A at 5 to 48 VDC		G3R-ODX02SN
			1.5 A at 48 to 200 VDC		G3R-OD201SN

Note: When ordering a TÜV approved model, add "-UTU" to the model number as shown below: Example: G3R-OA202SZN-UTU.

■ I/O Indication

 $\mbox{I/O}$ module classification and AC/DC use are indicated on the mark affixed to the top of the product.

Mark indication	Specification
AC IN	Input module, AC input
DC IN	Input module, DC input
AC OUT	Output module, AC output
DC OUT	Output module, DC output

Mark attached to the top of the product



Specifications

■ Ratings

Input Module

Input

Model	Rated voltage	Operating voltage	Input current	Must operate voltage	Must release voltage
G3R-IAZR1SN	100 to 240 VAC	60 to 264 VAC	15 mA max.	60 VAC max.	20 VAC min.
G3R-IDZR1SN	5 VDC	4 to 6 VDC	8 mA max.	4 VDC max.	1 VDC min.
	12 to 24 VDC	6.6 to 32 VDC		6.6 VDC max.	3.6 VDC min.
G3R-IDZR1SN-1	5 VDC	4 to 6 VDC		4 VDC max.	1 VDC min.
	12 to 24 VDC	6.6 to 32 VDC		6.6 VDC max.	3.6 VDC min.

Output

Model	Logic level supply voltage	Logic level supply current				
G3R-IAZR1SN	4 to 32 VDC	0.1 to 100 mA				
G3R-IDZR1SN						
G3R-IDZR1SN-1						

Output Module

Input

Model	Rated voltage	Operating voltage	Input current	Must operate voltage	Must release voltage
G3R-OA202SZN	5 to 24 VDC	4 to 32 VDC		4 VDC max.	1 VDC min.
G3R-OA202SLN			(at 25°C)		
G3R-ODX02SN			8 mA max.		
G3R-OD201SN					

Output

Model	Rated load voltage	Load voltage range	Load current (see note)	Inrush current
G3R-OA202SZN	100 to 240 VAC	75 to 264 VAC	0.05 to 2 A	30 A (60 Hz, 1 cycle)
G3R-OA202SLN				
G3R-ODX02SN	5 to 48 VDC	4 to 60 VDC	0.01 to 2 A	8 A (10 ms)
G3R-OD201SN	48 to 200 VDC	40 to 200 VDC	0.01 to 1.5 A	8 A (10 ms)

Note: The minimum current value is measured at 10°C min.

Characteristics

■ Input Module

Item	G3R-IAZR1SN	G3R-IDZR1SN	G3R-IDZR1SN-1						
Operate time	20 ms max.	0.1 ms max.	15 ms max.						
Release time	20 ms max.	0.1 ms max.	15 ms max.						
Response frequency	10 Hz	1 kHz	10 Hz						
Output ON voltage drop	1.6 V max.								
Leakage current	5 μA max.								
Insulation resistance	100 M Ω min. between input and	d output							
Dielectric strength	4,000 VAC, 50/60 Hz for 1 min. between input and output								
Vibration resistance	10 to 55 Hz, 1.5-mm double am	plitude							
Shock resistance	1,000 m/s ² {approx. 100G}								
Ambient temperature	Operating: -30°C to 80°C (with Storage: -30°C to 100°C (with r								
Approved standards	UL508 File No. E64562 CSA C22.2 (No. 14, No. 950) File No. LR35535 TÜV File No. R9650094 (EN60950)								
Ambient humidity	Operating: 45% to 85%								
Weight	Approx. 18 g								


■ Output Module

Item	G3R-OA202SZN	G3R-OA202SLN	G3R-ODX025N	G3R-OA201SN				
Operate time	1/2 of load power source cyc	cle + 1 ms max.	1 ms max.	•				
Release time	1/2 of load power source cyc	cle + 1 ms max.	2 ms max.					
Response frequency	20 Hz		100 Hz					
Output ON voltage drop	1.6 V max.			2.5 V max.				
Leakage current	1.5 mA max.		1 mA max.	•				
Insulation resistance	100 M Ω min. between input	and output						
Dielectric strength	4,000 VAC, 50/60 Hz for 1 m	nin. between input and outp	input and output					
Vibration resistance	10 to 55 Hz, 1.5-mm double	amplitude						
Shock resistance	1,000 m/s ² {approx. 100G}							
Ambient temperature	Operating: -30°C to 80°C (w Storage: -30°C to 100°C (wi							
Approved standards	UL508 File No. E64562 CSA C22.2 (No. 14, No. 950 TÜV File No. R9650094 (EN							
Ambient humidity	Operating: 45% to 85%							
Weight	Approx. 18 g							


Engineering Data

Load Current vs. Ambient Temperature Characteristics


G3R-OA202SZN/OA202SLN



G3R-ODX02SN (4 to 60 VDC)



G3R-OD201SN (40 to 200 VAC)




- Note: 1. When G730-Z0M04-B is mounted.
 - 2. When G70A-Z0C16 is mounted.


Inrush Current Resistivity

Non-repetitive (Keep the inrush current to half the rated value if it occurs repetitively.)


G3R-OA202SZN/OA202SLN



G3R-ODX02SN




G3R-OD201SN




Operation

■ Precaution of Mounting Output Modules

With up to four G3R SSRs mounted closely and side by side, 2-A loads can be switched.




With a G3R SSRs mounted every other slot, 2-A loads can be switched.




Dimensions

Unit: mm (inch)

■G3R





Terminal arrangement/ Internal connections (Bottom view)



■ Connecting Sockets


P2RF-05-E







- * Indicates a value when using the PFP-□N Supporting Rail with the P2RF-05-E The value is 71.5 when using the PFP-□N2.
- *** Indicates a value when using the PFP-□N Supporting Rail with the P2RF-08-E The value is 75.5 when using the PFP-□N2.

P2R-057P








■ Socket Mounting Plate

Use the Socket Mounting Plate when arranging several Sockets in a row.



■ Approvals

UL (File No. E64562)/CSA (File No. LR35535)

Model G3R-	Module type	Rating
IAZR1SN	Input	100 to 240 VAC
IDZR1SN	Input	5 VDC, 12 to 24 VDC
IDZR1SN-1	Input	5 VDC, 12 to 24 VDC
OA202SZN	Output	5 to 24 VDC
OA202SLN	Output	5 to 24 VDC
ODX02SN	Output	5 to 24 VDC
OD201SN	Output	5 to 24 VDC

Model G3R-	Module type	Output rating			
IAZR1SN	Input	32 VDC, 100 mA (General Purpose)			
IDZR1SN	Input	32 VDC, 100 mA (General Purpose)			
IDZR1SN-1	Input	32 VDC, 100 mA (General Purpose)			
OA202SZN	Output	264 VAC, 2 A (General Purpose)			
		264 VAC, 1 A (Tungsten)			
		264 VAC, 1 A FLA, 6 A LRA			
OA202SLN	Output	264 VAC, 2 A (General Purpose)			
		264 VAC, 1 A (Tungsten)			
		264 VAC, 1 A FLA, 6 A LRA			
ODX02SN	Output	60 VDC, 2 A (General Purpose)			
		60 VDC, 1 A (Tungsten)			
OD201SN	Output	200 VDC, 1.5 A (General Purpose)			
		200 VDC, 0.75 A (Tungsten)			

Precautions

See Technical Information section at the front of the Solid State Relay section of this catalog for solid state precautions.

■ Connection

With the SSR for DC switching, the load can be connected to either positive or negative output terminal of the SSR. $\frac{1}{2} \int_{-\infty}^{\infty} \frac{1}{2} \int_{-\infty}^{\infty} \frac{1}{2}$

■ Protective element

Since the SSR does not incorporate an overvoltage absorption component, be sure to connect an overvoltage absorption component when using the SSR under an inductive load.



MEM	IEMO																				
:		:	:		· ,	:	1	1	:	:	:	1	1	·	:		·	:	:	,	
	:	:	;	:	 	;	;	;	;	;	;	1	;	·	;		·	;	;	!	
, * , , ,	((1	1		1	1	1	1	1	1	r 1 	1	, ·	1	, ·	, ·	1	1	1	
4		:	;	1	 	1	:	:	1	;	;	:	:		1			1	1	!	
, • , I			,			1	1	1	1	,	,	1	1		1			1	1	1	
	:	:			· ;	1	1	1	1			1	1	·	1		·	1	1	1	
	1																				
	1	:	;		 	1	1	1	1	;	;	1	1		1			1	1	1	
	1	1			:	1	1	1	1				1		1	·		1	1	1	
			1							1											
	4		,		! ! ;					,	,	 								1	
		:			 	· ·	:	:	· ·				:		· ·			· ·	· ·		
1																					
1	1	1		1 1	 	· ;	i	i	· ;			 	i		· ;			· ;	· ;	1	
+ 1			;	:	 	; ;	1	1	; ;	;	;	1 1	1		; ;			; ;	; ;	1	
		1	:							:	:										
										1											
	1	1	1		k 4		1				4	1	1	· ·						· i	
		1					1	 	1	;											
				· (
+		1	:	1	F 1	1	:	:					:							1	
		4			h 4		4	4	4			4	4		4			4	4		
																			i i		
6	4						:	:					:								
				4	h 4	4	4	4	4				4		4			4	:	4	
	1																				
8	1	1		1	1	1	1	1	1			4	1		1			1	1		
	1	(1	:	:	1	1	:				1		:			1			
		1																			
		:	:	:	:		:	:		:	:	:	:		:			:		:	

Terms and Conditions of Sale

- Offer: Acceptance. These terms and conditions (these "Terms") are deemed part of all quotations, acknowledgments, invoices, purchase orders and other documents, whether electronic or in writing, relating to the sale of products or services (collectively, the "Products") by Omron Electronic Components LLC ("Seller"). Seller hereby objects to any terms or conditions proposed in Buyer's purchase order or other documents which are inconsistent with, or in addition to, these Terms.
- Prices: Payment. All prices stated are current, subject to change without notice by Seller. Buyer agrees to pay the price in effect at time of shipment. Payments for Products received are due net 30 days unless otherwise stated
- <u>Discounts.</u> Cash discounts, if any, will apply only on the net amount of invoices sent to Buyer after deducting transportation charges, taxes and duties, and will be allowed only if (i) the invoice is paid according to Seller's
- payment terms and (ii) Buyer has no past due amounts owing to Seller. Currencies. If the prices quoted herein are in a currency other than U.S. dol lars, Buyer shall make remittance to Seller at the then current exchange rate most favorable to Seller and which is available on the due date; provided that if remittance is not made when due, Buyer will convert the amount to U.S. dol-lars at the then current exchange rate most favorable to Seller available during the period between the due date and the date remittance is actually made.
- Governmental Approvals. Buyer shall be responsible for, and shall bear all costs involved in, obtaining any government approvals required for the importation or sale of the Products.
- Taxes. All taxes, duties and other governmental charges (other than general real property and income taxes), including any interest or penalties thereon, imposed directly or indirectly on Seller or required to be collected directly or indirectly by Seller for the manufacture, production, sale, delivery, importation, consumption or use of the Products sold hereunder (including customs duties and sales, excise, use, turnover and license taxes) shall be charged to and remitted by Buyer to Seller.
- Financial. If the financial position of Buyer at any time becomes unsatisfactory to Seller, Seller reserves the right to stop shipments or require satisfactory security or payment in advance. If Buyer fails to make payment or otherwise comply with these Terms or any related agreement, Seller may (without liability and in addition to other remedies) cancel any unshipped portion of Products sold hereunder and stop any Products in transit until Buyer pays all amounts, including amounts payable hereunder, whether or not then due, which are owing to it by Buyer. Buyer shall in any event remain liable for all unpaid
- <u>Cancellation; Etc.</u> Orders are not subject to rescheduling or cancellation unless Buyer indemnifies Seller fully against all costs or expenses arising in connection therewith
- Force Majeure. Seller shall not be liable for any delay or failure in delivery resulting from causes beyond its control, including earthquakes, fires, floods, strikes or other labor disputes, shortage of labor or materials, accidents to machinery, acts of sabotage, riots, delay in or lack of transportation or the requirements of any government authority.

 10. Shipping: Delivery.

 1. Shipments shall be by a carrier selected by Seller:
- - Such carrier shall act as the agent of Buyer and delivery to such carrier shall constitute delivery to Buyer;
 - 3. All sales and shipments of Products shall be FOB shipping point (unless otherwise stated in writing by Seller), at which point title to and all risk of loss of the Products shall pass from Seller to Buyer, provided that Seller shall retain a security interest in the Products until the full purchase price is paid by Buver:
- paid by Buyer;

 4. Delivery and shipping dates are estimates only.

 5. Seller will package Products as it deems proper for protection against normal handling and extra charges apply to special conditions.

 11. Claims. Any claim by Buyer against Seller for shortage or damage to the Products occurring before delivery to the carrier must be presented in writing to Seller within 30 days of receipt of shipment and include the original transportation bill signed by the carrier noting that the carrier received the Products from Seller in the condition claimed.

- 12. <u>Warranties.</u> (a) <u>Exclusive Warranty</u>. Seller's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Seller (or such other period expressed twelve months from the date of sale by Seller (or such other period expressed in writing by Seller). Seller disclaims all other warranties, express or implied. (b) Limitations. SELLER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. Seller further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or othany type for clams or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) <u>Buyer Remedy</u>. Seller's sole obligation hereunder shall be to replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the noncomplying Product or, at Seller's election, to repay or credit Buyer an amount equal to the purchase price of the Product; provided that in no event shall Seller be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Seller's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of ject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Seller before shipment. Seller shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies, or any other materials or substances or environ-
- circuits, system assembles, or any other materials of substances of environments. Any advice, recommendations or information given orally or in writing are not to be construed as an amendment or addition to the above warranty. Limitation on Liability: Etc. SELLER SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY. Further, in no event shall liability of Seller exceed the individual price of the Product on which liability is asserted.
- which liability is asserted.
 <u>Indemnities</u>. Buyer shall indemnify and hold harmless Seller, its affiliates and its employees from and against all liabilities, losses, claims, costs and expenses (including attorney's fees and expenses) related to any claim, investigation, litigation or proceeding (whether or not Seller is a party) which arises or is alleged to arise from Buyer's acts or omissions under these Terms or in any way with respect to the Products. Without limiting the foregoing, Buyer (at its own expense) shall indemnify and hold harmless Seller and defend or settle any action brought against Seller to the extent that it is based on a claim that any Product made to Buyer specifications infringed intellectual property rights
- of another party.

 Property: Confidentiality. The intellectual property embodied in the Products is the exclusive property of Seller and its affiliates and Buyer shall not attempt to duplicate it in any way without the written permission of Seller. Notwithstand to the product of the property of the product of the produc ing any charges to Buyer for engineering or tooling, all engineering and tooling shall remain the exclusive property of Seller. All information and materials supplied by Seller to Buyer relating to the Products are confidential and proprietary, and Buyer shall limit distribution thereof to its trusted employees and
- etary, and Buyer shall limit distribution thereof to its trusted employees and strictly prevent disclosure to any third party.

 16. Miscellaneous. (a) Waiver. No failure or delay by Seller in exercising any right and no course of dealing between Buyer and Seller shall operate as a waiver of rights by Seller. (b) Assignment. Buyer may not assign its rights hereunder without Seller's written consent. (c) Law. These Terms are governed by Illinois law (without regard to conflict of law principles). Federal and state courts in Illinois shall have exclusive jurisdiction for any dispute hereunder. (d) Amendment. These Terms constitute the entire agreement between Buyer and Seller relating to the Products, and no provision may be changed or waived unless in writing signed by the parties. (e) Severability. If any provision hereof is rendered ineffective or invalid such provision shall not invalidate any hereof is rendered ineffective or invalid, such provision shall not invalidate any other provision. (f) Setoff. Buyer shall have no right to set off any amounts against the amount owing in respect of this invoice.. (g) Definitions. As used herein, "including" means "including without limitation".

Certain Precautions on Specifications and Use

- Suitability for Use. Seller shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in Buyer's application or use of the Product. At Buyer's request, Seller will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the partic-Buyer shall be solely responsible for determining appropriateless of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases but the following is a non-exhaustive list of applications for which particular attention must be given:

 (i) Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this document.

 - (ii) Energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.

(iii)Use in consumer products or any use in significant quantities. (iv)Systems, machines and equipment that could present a risk to life or property. Please know and observe all prohibitions of use applicable to this

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

- Programmable Products. Seller shall not be responsible for the user's
- programming of a programmable product, or any consequence thereof.

 Performance Data. Performance data given in this publication is provided as a guide for the user in determining suitability and does not constitute a warranty It may represent the result of Seller's test conditions, and the users must corre late it to actual application requirements. Actual performance is subject to Seller's Warranty and Limitations of Liability.
- Change in Specifications. Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our pract tice to change part numbers when published ratings or features are changed or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for you application. Please consult with your Seller representative at any time to con firm actual specifications of purchased Product.

 <u>Errors and Omissions</u>. The information in this publication has been carefully

checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors, or omissions.

RoHS Compliance. Where indicated, our products currently comply, to the bes

of our knowledge as of the date of this publication, with the requirements of the European Union's Directive on the Restriction of certain Hazardous Sub stances ("RoHS"), although the requirements of RoHS do not take effect until July 2006. These requirements may be subject to change. Please consult our website for current information. website for current information.

Complete "Terms and Conditions of Sale" for product purchase and use are on Omron's website at www.components.omron.com - under the "About Us" tab, in the Legal Matters section.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON ELECTRONIC COMPONENTS LLC

55 E. Commerce Drive, Suite B Schaumburg, IL 60173

847-882-2288

OMRON CANADA, INC.

885 Milner Avenue Toronto, Ontario M1B 5V8

416-286-6465

OMRON ON-LINE

Global - http://www.omron.com USA - http://www.components.omron.com Canada - http://www.omron.ca