


Data Sheet

Type Number 6320
Designation IEC CR 2320
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition:..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 135 mAh
 Load 10 kOhm, at 20°C down to 2 V



Weight (approx.) 2,9 g
Volume 0,8 ccm
Coding..... Manufacturing Month/Year

Temperature Ranges

	min	max.
Storage	-55°C	70 °C
Discharge	-20°C	70°C

Dimensions

	min	max.
Diameter (A)	22,7	23
Height (B)	1,75	2
Shoulder Diameter[E].....		
Shoulder Height [C].....		

Segment Electronic

Main Applications Watch
 Photo
 Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w Current [μ A]:	10000 Ω	Time: Capacity [mAh]: Energy [MWh]:	470 h 135 385

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!
 Date of issue: 03-09-25