


Customers:		Edition: A	Revision: 1	
Customer Part No.:		BCc Part No.: D390G25C0GH63L2R		
Rated Voltage: 100 VDC	Test Voltage: 250 VDC	12NC: 228250602354	Qualification: IEC	
Capacitance: 39.00pF	Tolerance: ± 2%	Cap.Range: 38.22pF To 39.78pF		
DF/Q: At Q = 1000 MIN 1MHZ/1.0VRMS		Temp.chart./coefficient: NP0	Operating Temp.: -55°C to 125°C	
Coating: Phenolic	SPQ: 1000PCS	Insulation Resistance: 10G Ω MIN		
Marking: <div style="text-align: center;"> <u>C0</u> <u>39G</u> </div>		Dimensions(mm)		
		D-Body Diameter: 6.5 MAX		
		T-Body Thickness: 3.5 MAX		
		F-Lead Spacing: 2.5 ± 0.8		
		V-S Spacing: NA		
		L-Lead Length: 30 ± 5		
		SH-Seat Height: N/A		
		DR-Run Down: 1.5 MAX		
		ED-Disc Exposure: N/A		
		K-Kink Off: NA		
G-Lead Diameter: 0.6±0.05				
Resistance to Soldering Heat: 260±5°C, 10±1s		θ-Kink Angle: NA		
Packing: Bulk		Lead Style: L		
Taping Specifications(mm)				
Pitch between Components	P			
Feed-hole Pitch	P0			
Feed-hole Diameter	D0			
Height to Seating Plane	H0			
Top of Component Height	H1			
Carrier Tape Width	W			
Remarks/Customers specific requirements:				