


Customers:		Edition: A	Revision: 2
Customer Part No.:		BCc Part No.: D122K20Y5PH63L2R	
Rated Voltage: 100 VDC	Test Voltage: 250 VDC	12NC: 228261602071	Qualification: IEC
Capacitance: 1200.00pF	Tolerance: ± 10%	Cap.Range: 1080.00pF To 1320.00pF	
DF/Q: 2.5% MAX	At 1KHZ/1.0VRMS	Temp.chart./coefficient: Y5P	Operating Temp.: -30°C to 125°C
Coating: Phenolic	SPQ: 1000PCS	Insulation Resistance: 10G Ω MIN	
Marking: <div style="text-align: center; margin-top: 20px;"> <u>122</u> </div>		Dimensions(mm)	
		D-Body Diameter: 5 MAX	
		T-Body Thickness: 3.5 MAX	
		F-Lead Spacing: 2.5 ± 0.8	
		V-S Spacing: NA	
		L-Lead Length: 30 ± 5	
		SH-Seat Height: N/A	
		DR-Run Down: 1.5 MAX	
		ED-Disc Exposure: N/A	
		K-Kink Off: NA	
		G-Lead Diameter: 0.6±0.05	
		Resistance to Soldering Heat: 260±5°C,10±1s	
Packing: Bulk	Lead Style: L		
Taping Specifications(mm)			
Pitch between Components	P		
Feed-hole Pitch	P0		
Feed-hole Diameter	D0		
Height to Seating Plane	H0		
Top of Component Height	H1		
Carrier Tape Width	W		
Remarks/Customers specific requirements:			