



NOTES:

1. MATERIAL -
PHOSPHOR BRONZE CDA 521
THICKNESS: (0.200) ± 0.008
TENSILE STRENGTH: 655-760 N/mm²
PLATING - SEE SHEET 2
2. FOR DIMENSIONS A, B, C, D, F & G
SEE SHEET 2
3. FOR WIRE SIZE & INSULATION DIA
SEE SHEET 2
4. THIS TERMINAL TO MATE WITH
(0.635) ± 0.025 SQUARE PIN
5. MAX BURR AFTER CUT-OFF
(0.025) ± 0.001

REMOVED LEAD REF. ECN NO. E2006-0155 DRAWN: JDENNEHY 2005/08/29 CHKD: DMORIARTY 2005/08/29 APPR: JDENNEHY 2005/09/05	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		mm	INCH	DRAWN BY NPC	DATE 1987/08/27	TITLE C-GRID III FEMALE CRIMP TERMINAL				
REV	DESCRIPTION	4 PLACES ± ---	± ---	CHECKED BY D.MORIARTY	DATE 2005/08/26	MOLEX INCORPORATED				
		3 PLACES ± ---	± 0.004	APPROVED BY JDENNEHY	DATE 2005/08/26					
		2 PLACES ± 0.1	± 0.008	MATERIAL NO. SD-90119		DOCUMENT NO. SD-90119		SHEET NO. 1 OF 2		
		1 PLACE ± 0.2	± ---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
		ANGULAR ± 5 °		SEE CHART						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

PPL PLA LD O D P N

	Λ
0 0	Ε
0	Γ
0 20	Λ
0 2	Ε
0 22	Γ
2 09	Λ
2 0	Ε
2	Γ
2 20	Λ
2 2	Ε
	Γ

