



MBRB2035CT THRU MBRB2060CT

SCHOTTKY RECTIFIER

Reverse Voltage - 35 to 60 Volts Forward Current - 20.0 Amperes

TO-263AB



Dimensions in inches and (millimeters)

FEATURES

- ◆ Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- ◆ Dual rectifier construction, positive center tap
- ◆ Metal silicon junction, majority carrier conduction
- ◆ Low power loss, high efficiency
- ◆ High current capability, low forward voltage drop
- ◆ High surge capability
- ◆ Guardring for overvoltage protection
- ◆ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ◆ High temperature soldering in accordance with CECC 802 / Reflow guaranteed



MECHANICAL DATA

Case: JEDEC TO-263AB molded plastic

Terminals: Leads solderable per MIL-STD-750, Method 2026

Polarity: As marked

Mounting Position: Any

Weight: 0.08 ounce, 2.24 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

| | SYMBOLS | MBRB2035CT | MBRB2045CT | MBRB2050CT | MBRB2060CT | UNITS |
|--|--|-------------------|---------------------------|-------------------|------------------------------|--------------|
| Maximum repetitive peak reverse voltage | V _{RRM} | 35 | 45 | 50 | 60 | Volts |
| Maximum working peak reverse voltage | V _{RWM} | 35 | 45 | 50 | 60 | Volts |
| Maximum DC blocking voltage | V _{DC} | 35 | 45 | 50 | 60 | Volts |
| Maximum average forward rectified current at T _C =135°C | I _(AV) | | | 20.0 | | Amps |
| Peak repetitive forward current per leg at T _C =135°C (rated V _R , sq. wave 2.0 KHz) | I _{FRM} | | | 20.0 | | Amps |
| Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) | I _{FSM} | | | 150.0 | | Amps |
| Peak repetitive reverse surge current (NOTE 1) | I _{RRM} | | 1.0 | | 0.5 | Amps |
| Maximum instantaneous forward voltage per leg at (NOTE 2) | I _F =10A, T _C =25°C I _F =10A, T _C =125°C I _F =20A, T _C =25°C I _F =20A, T _C =125°C | V _F | — 0.57 0.84 0.72 | | 0.80 0.70 0.95 0.85 | Volts |
| Maximum instantaneous reverse current at rated DC blocking voltage per leg | I _R | 0.1 15.0 | | 0.15 150.0 | | mA |
| Voltage rate of change, (rated V _R) | dV/dt | | | 10,000 | | V/μs |
| Typical thermal resistance per leg (NOTE 3) | R _{θJC} | | | 2.0 | | °C/W |
| Operating junction temperature range | T _J | | | -65 to +150 | | °C |
| Storage temperature range | T _{STG} | | | -65 to +175 | | °C |

NOTES:

(1) 2.0μs pulse width, f=1.0KHz

(2) Pulse test: 300μs pulse width, 1% duty cycle

(3) Thermal resistance from junction to case per leg

RATINGS AND CHARACTERISTIC CURVES MBRB2035CT THRU MBRB2060CT

