

The New 16th Edition (BS EN 61557) testers from Martindale give high quality, accurate testing at low costs. These British made meters comply fully with all UK and international standards. The range has a low cost 500V insulation tester and a competitively priced 250/500/1000V tester as well as economical Loop and RCD testers.



All 16th Edition meters come with this rugged fabric carry case.

IN2001



The IN2001 insulation tester is amazing value for money. You can now do 16th Edition testing with the proper equipment at very low cost.

With an automatic zero adjust feature to remove the resistance of the leads, you are guaranteed fast, accurate continuity testing.

A major advantage of this design is that you can set the test button to be either latching to give a permanent output or 'press to test' with the option of switching between these two ways of working at any time. A professional product for professional electricians!

IN2001: insulation test at 500V.
0-200Ω continuity range (buzz < 1Ω),
0.01Ω resolution.
0-100MΩ.
500V AC range.
Complies with BS EN 61557 (16th Edition).
Dimensions: 190 x 90 x 54mm.
Replacement leads - order code: TL47.
Optional fused test leads - order code: TL57.
Supplied with batteries, instructions, quality case and leads.

IN2003



The IN2003 insulation and continuity tester gives 250, 500 & 1000V tests.

The top of the range IN2003 insulation tester comes with all the facilities you need to do professional testing.

With an automatic zero adjust feature to remove the resistance of the leads, you are guaranteed fast, accurate continuity testing. The three test voltages allow you to carry out the widest range of testing.

A major advantage of this design is that you can set the test button to be either latching to give a permanent output or 'press to test' with the option of switching between these two ways of working at any time. A professional product for professional electricians!

IN2003: insulation test at 250 / 500 / 1000V.
0-200Ω continuity range (buzz < 1Ω),
0.01Ω resolution.
0-100MΩ (500V) 0-200MΩ (1000V).
500V AC range.
Complies with BS EN 61557 (16th Edition).
Dimensions: 190 x 90 x 54mm.
Replacement leads - order code: TL47.
Optional fused test leads - order code: TL57.
Supplied with batteries, instructions, quality case and leads.