


Data Sheet

Type Number: 4276
 Designation IEC: LR 44
 System: Manganese dioxide /
 Zinc / KOH - Electrolyte
 Nominal Voltage [V]: 1,5
 Typical Capacity C [mAh]: 125
 Load 5.6 kOhm, at 20 °C down to 1.2 V
 Weight, approx [g]: 1,8
 Volume [ccm]: 0,51
 Coding: Manufacturing Month/Year
 by Letter Code



Temperature Ranges [° C]: **min.** **max.**
 Storage: -10 65
 Discharge: -10 65
 Dimensions [mm]: **min.** **max.**
 Diameter : 11,25 11,6
 Height [A/B]: 5 5,4

Segment: Electronic
 Main Applications: Watch
 Photo
 Electronic

Typical Capacities (at 20° C):

Discharge Type:	Load	End Voltage	1.2 V
Continuous	5600	Ω Time:	482 h
24h/d, 7d/w		Capacity [mAh]:	125
Current [µA]: 270		Energy [mWh]:	168