


**Data Sheet**

Type Number: ..... 4626  
 Designation IEC: ..... LR 9  
 System: ..... Manganese dioxide /  
 Zinc / KOH - Electrolyte  
 Nominal Voltage [V]: ..... 1,5  
 Typical Capacity C [mAh]: ..... 200  
 Load 300 Ohm, at 20 °C down to 0.9 V  
 Weight, approx [g]: ..... 3,3  
 Volume [ccm]: ..... 1,01  
 Coding: ..... Manufacturing Month/Year  
 by Letter Code



Temperature Ranges [° C]:                      **min.**        **max.**  
 Storage: .....                                      -10            65  
 Discharge: .....                                   -10            65  
 Dimensions [mm]:                                **min.**        **max.**  
 Diameter : .....                                    15            15,5  
 Height [A/B]: .....                                5,6            6,1

Segment: ..... Photo  
 Main Applications: ..... Photo  
 Electronic  
 Car Alarm

**Typical Capacities (at 20° C):**

Discharge Type:	Load	End Voltage	0.9 V
Continuous	300	Ω Time:	48 h
24h/d, 7d/w		Capacity [mAh]:	200
Current [µA]: 5000		Energy [mWh]:	250