

**Data Sheet**

Type Number: ..... 4074  
 Designation IEC: ..... 10 LR 54  
 System: ..... Manganese dioxide /  
 Zinc / KOH - Electrolyte

UL Recognition: ..... ---

Nominal Voltage [V]: ..... 15

Typical Capacity C [mAh]: ..... 45

Load 110 kOhm, at 20 °C down to 11.0 V

Weight, approx [g]: ..... 14

Volume [ccm]: ..... 6,63

Coding: ..... Manufacturing Month/Year  
 by Letter Code

Temperature Ranges [°C]: **min. max.**  
 Storage: ..... -10 65  
 Discharge: ..... -10 65

Dimensions [mm]: **min. max.**  
 Diameter [A]: ..... 14 16  
 Height [B]: ..... 33 35  
 Shoulder Diameter[L]: ..... 7  
 Shoulder Height [M]: ..... 1,3

Segment: ..... Photo

Main Applications: ..... Photo  
 Electronic

**Typical Capacities (at 20° C):**

Discharge Type:	Load	End Voltage	11 V
Continuous	110000 Ω	Time:	380 h
24h/d, 7d/w		Capacity [mAh]:	45
Current [µA]: 136		Energy [mWh]:	590

