

## SDE Options and available Dies

### Tool Options



360170



4132518

Tool - without dies	Mfrs. List No.	Order Code	Price Each
Procrimper III	354940-1	<b>360-170</b>	
PEW 12	9-1478240-0	<b>413-2440</b>	

### SDE Dies

SDE or Standard Die Envelope is an innovation from Tyco Electronics that provides cost effective flexibility through a common die outline.

414615

Product Type	Wire Size: mm - (AWG)	Mfrs. List No.	Order Code	Price Each
PIDG & Plasti-grip	0.40 - 6.0 (22 - 10)	58423-1	<b>360-326</b>	
HD20 & HDP-20	0.08 - 0.6 (28 - 20)	58448-3	<b>360-259</b>	
HDP-22	0.08 - 0.4 (28 - 22)	90800-2	<b>962-9505</b>	
Multimate	0.80 - 1.5 (28 - 16)	58495-2	<b>360-200</b>	
Superseal 1.5 series	0.50 - 1.0 (21 - 18)	58583-2	<b>962-9637</b>	
Circular DIN 72585	1.00 - 2.5 (18 - 14)	58606-2	<b>962-9629</b>	
PE Series - 4.2mm	0.15 - 0.4 (26 - 22)	91387-2	<b>811-6300</b>	
PE Series - 4.2mm	0.40 - 1.0 (22 - 18)	91388-2	<b>811-6318</b>	
AMP Modu	0.15 - 0.4 (26 - 22)	58641-2	<b>962-9580</b>	
Mate-N-Lok 3.5mm / 0.14"	0.60 - 2.5 (20 - 14)	1752938-2	<b>857-8230</b>	
Universal Mate-N-Lok	0.20 - 1.0 (24 - 18)	90548-2	<b>962-9548</b>	
Universal Mate-N-Lok	0.60 - 2.5 (20 - 14)	58637-2	<b>962-9599†</b>	
Universal Mate-N-Lok	0.60 - 2.5 (20 - 14)	90547-2	<b>360-272†</b>	
Commercial Mate-N-Lok	0.20 - 1.0 (24 - 18)	90574-2	<b>962-9530</b>	
Commercial Mate-N-Lok	0.60 - 2.5 (20 - 14)	90575-2	<b>360-302</b>	
Mini Universal Mate-N-Lok & 0.15 - 0.4 (26 - 22)				
Mini-CPC		90758-2	<b>962-9521</b>	
Mini Universal Mate-N-Lok & 0.40 - 1.0 (22 - 18)				
Mini-CPC		90759-2	<b>421-3841</b>	
Mini Universal Mate-N-Lok & 0.60 - 1.5 (20 - 16)				
Mini-CPC		90760-2	<b>962-9513</b>	
Micro MATE-N-LOK	0.05 - 0.6 (30 - 20)	91391-2	<b>111-1472</b>	
Greenpar	RG58, 59, URM 70, Belden 9907, BT 2002	9-1478242-0	<b>413-2452</b>	
Greenpar	RG 174, 179, BT 3002	9-1478245-0	<b>413-2476</b>	
Greenpar	RG18, 9, 213	9-1478246-0	<b>413-2488</b>	
Greenpar	RG 174, 178	9-1478248-0	<b>413-2506</b>	

† 9629599 = Insulation diameter 3.30mm (0.13") max

† 360272 = Insulation diameter 5.08mm (0.20") max