


Lower Voltage Ceramic Disc Capacitors 2 kV_{DC} to 7.5 kV_{DC}

Fig. 1



LEAD OFFSET 'LO'		
NOMINAL	~ THICKNESS - 0.100"	
EXCEPTION	0.07" (1.8 mm)	-565R20GAP10
	0.08" (2.0 mm)	-565R30GASS20
	0.10" (2.54 mm)	-565R30GASS33

INSULATION RESISTANCE

2 kV _{DC}	min. 10 000 MΩ
3 kV _{DC}	min. 50 000 MΩ
6 kV _{DC}	min. 75 000 MΩ
7.5 kV _{DC}	min. 200 000 MΩ

TOLERANCE ON CAPACITANCE

± 10 %, ± 20 %, - 20 % to + 80 %

DISSIPATION FACTOR

0.2 % max. at 1 MHz; 1 V
2.0 % max. at 1 kHz; 1 V

CATEGORY TEMPERATURE RANGE

- 25 °C to + 85 °C

CLIMATIC CATEGORY ACC. TO EN60068-1

25/085/21

OPERATING TEMPERATURE RANGE

- 25 °C to + 105 °C

FEATURES

- Low losses
- High capacitance in small sizes
- High stability
- Radial leads
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT

APPLICATIONS

- Lighting ballasts
- SMPS
- DC and pulse high voltage

DESIGN

The capacitors consist of a ceramic disc of which both sides are silver-plated. Connection leads are made of tinned copper having diameters of 0.025" (0.64 mm) or 0.032" (0.81 mm).

The capacitors may be supplied with radial kinked or straight leads having lead spacing of 0.250" (6.35 mm) or 0.375" (9.5 mm) or 0.500" (12.7 mm)

The standard tolerances are ± 10 % or ± 20 %.

Coating is made of resin coating or flame retardant epoxy resin in accordance with "UL 94 V-0".

CAPACITANCE RANGE

10 pF to 0.10 μF

RATED VOLTAGE

2 kV_{DC}
3 kV_{DC}
6 kV_{DC}
7.5 kV_{DC}

DIELECTRIC STRENGTH BETWEEN LEADS

Component test:

2 kV _{DC}	3500 V _{DC} , 2 s
3 kV _{DC}	5000 V _{DC} , 2 s
6 kV _{DC}	10 500 V _{DC} , 2 s
7.5 kV _{DC}	11 250 V _{DC} , 2 s

CERAMIC DIELECTRIC

C0G, U2J, R3L, (Class 1)
X7R, X5F, X5S, Y5S, Y5U, Y5V, Z5U (Class 2)

564R and 565R Series



Vishay Cera-Mite

Lower Voltage Ceramic Disc Capacitors
2 kV_{DC} to 7.5 kV_{DC}

ORDERING INFORMATION, CERAMIC 2 kV _{DC}											
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE INCH (mm)	WIRE SIZE		ORDERING CODE				
					AWG	INCH (mm)					
X7R											
100	± 10 %	0.330 (8.4)	0.190 (4.8)	0.250 (6.4)	20	0.032 (0.81)	564R20TST10				
220			0.180 (4.6)				564R20TST22				
330			564R20TST33								
470			0.170 (4.3)				564R20TST47				
560			0.185 (4.7)				564R20TST56				
680			0.170 (4.3)				564R20TST68				
1000		0.400 (10.2)	0.175 (4.4)				564R20TSD10				
1500		0.430 (10.9)	0.160 (4.1)				564R20TSD15				
1800		0.460 (11.7)	0.170 (4.3)				564R20TSD18				
2200							564R20TSD22				
2700							564R20TSD27				
3300		0.530 (13.5)	0.170 (4.3)				564R20TSD33				
3900		0.680 (17.3)	0.170 (4.3)				564R20TSD39				
4700							564R20TSD47				
							0.375 (9.5)				
Y5S											
1000	± 20 %	0.330 (8.4)	0.175 (4.4)	0.250 (6.4)	20	0.032 (0.81)	564R20TSSD10				
1500		0.400 (10.2)	0.170 (4.3)				564R20TSSD15				
1800		0.430 (10.9)					564R20TSSD18				
2200		0.460 (11.7)					564R20TSSD22				
2700		0.530 (13.5)	0.175 (4.4)				564R20TSSD27				
3300							564R20TSSD33				
3900							564R20TSSD39				
4700		0.620 (15.7)	0.170 (4.3)				564R20TSSD47				
5600		0.680 (17.3)					564R20TSSD56				
6800		0.720 (18.3)					564R20TSSD68				
Y5U											
1000		± 20 %	0.330 (8.4)				0.170 (4.3)	0.250 (6.4)	20	0.032 (0.81)	564R20GAD10
1500	0.330 (8.4)		0.170 (4.3)	564R20GAD15							
Z5U											
1800	± 20 %	0.360 (9.1)	0.170 (4.3)	0.250 (6.4)	20	0.032 (0.81)	564R20GAD18				
2200		0.400 (10.2)	0.175 (4.4)				564R20GAD22				
2700		0.430 (10.9)					564R20GAD27				
3300							564R20GAD33				
3900		0.490 (12.4)	0.170 (4.3)				564R20GAD39				
4700							564R20GAD47				
6800		0.560 (14.2)	0.170 (4.3)				564R20GAD68				
0.010 μF		0.680 (17.3)					564R20GAS10				
Y5V											
0.01 μF	± 20 %	0.620 (15.7)	0.170 (4.3)	0.375 (9.5)	20	0.032 (0.81)	564R20GASS10				
0.05 μF		0.950 (24.1)	0.174 (4.4)		20		564R20GAS50				
0.10 μF		0.950 (24.1)	0.240 (6.1)		22	0.025 (0.64)	565R20GAP10				

TAPE AND REEL OPTIONS

- To specify tape and reel, add two letter suffix to the ordering code (for details of the packaging code see general section of the catalog)



ORDERING INFORMATION, CERAMIC 3 kV _{DC}								
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE INCH (mm)	WIRE SIZE		ORDERING CODE	
					AWG	INCH (mm)		
U2J (N750)								
10	± 20 %	0.330 (8.4)	0.210 (5.3)	0.250 (6.4)	20	0.032 (0.81)	564R30GAQ10	
12			0.210 (5.3)				564R30GAQ12	
15			0.180 (4.6)				564R30GAQ15	
R3L (N2200)								
22	± 20 %	0.330 (8.4)	0.200 (5.1)	0.250 (6.4)	20	0.032 (0.81)	564R30GAQ22	
27			0.190 (4.8)				564R30GAQ27	
33			0.170 (4.3)				564R30GAQ33	
X7R								
47	± 20 %	0.330 (8.4)	0.230 (5.8)	0.250 (6.4)	20	0.032 (0.81)	564R30GAQ47	
56			0.190 (4.8)				564R30GAQ56	
68			0.200 (5.1)				564R30GAQ68	
100			0.180 (4.6)				564R30GAT10	
150			0.190 (4.8)				564R30GAT15	
220			0.175 (4.4)				564R30GAT22	
270			0.180 (4.6)				564R30GAT27	
330			0.175 (4.4)				564R30GAT33	
390			0.180 (4.6)				564R30GAT39	
470			0.180 (4.6)				564R30GAT47	
680	± 10 %	0.400 (10.2)	0.175 (4.4)	0.375 (9.5)			564R30TST68	
1000			0.175 (4.4)				564R30TSD10	
1500			0.185 (4.7)				564R30TSD15	
1800			0.185 (4.7)				564R30TSD18	
2200			0.180 (4.6)				564R30TSD22	
2700			0.185 (4.7)				564R30TSD27	
3300			0.170 (4.3)				564R30TSD33	
3900			0.185 (4.7)				564R30TSD39	
4700			0.175 (4.4)				564R30TSD47	
6800			0.185 (4.7)				564R30TSD68	
Y5S								
1000	± 20 %	0.400 (10.2)	0.190 (4.8)	0.250 (6.4)	20	0.032 (0.81)	564R30TSSD10	
1500		0.460 (11.7)					564R30TSSD15	
1800		0.490 (12.4)					564R30TSSD18	
2200		0.530 (13.5)					564R30TSSD22	
2700		0.560 (14.2)					564R30TSSD27	
3300		0.620 (15.7)	0.185 (4.7)	0.375 (9.5)	564R30TSSD33			
3900		0.680 (17.3)	564R30TSSD39					
4700		0.790 (20.0)	0.190 (4.8)		564R30TSSD47			
5600		0.900 (22.9)	0.205 (5.2)		564R30TSSD56			
6800		0.205 (5.2)	564R30TSSD68					
Y5U								
680	± 20 %	0.330 (8.4)	0.175 (4.4)	0.250 (6.4)	20	0.032 (0.81)	564R30GAT68	
Z5U								
1000	± 20 %	0.330 (8.4)	0.195 (5.0)	0.250 (6.4)	20	0.032 (0.81)	564R30GAD10	
1500		0.360 (9.1)	564R30GAD15					
1800		0.400 (10.2)	0.190 (4.8)				564R30GAD18	
2200		0.430 (10.9)	0.200 (5.1)				564R30GAD22	
2700		0.460 (11.7)	0.185 (4.7)				564R30GAD27	
3300		0.490 (12.4)	0.185 (4.7)	0.375 (9.5)	564R30GAD33			
3900		0.530 (13.5)			564R30GAD39			
4700		0.620 (15.7)			564R30GAD47			
6800		0.680 (17.3)			564R30GAD68			
8200		0.790 (20.0)			564R30GAD82			
0.010 μF		0.720 (18.3)	0.265 (6.7)	22	0.025 (0.64)	565R30GASS20		
0.020 μF		0.900 (22.9)	0.240 (6.1)			565R30GASS33		
0.033 μF								
Y5V								
0.010 μF		± 20 %	0.720 (18.3)	0.185 (4.7)	0.375 (9.5)	20	0.032 (0.81)	564R30GASS10

TAPE AND REEL OPTIONS

- To specify tape and reel, add two letter suffix to the ordering code (for details of the packaging code see general section of the catalog)



564R and 565R Series

Lower Voltage Ceramic Disc Capacitors
2 kV_{DC} to 7.5 kV_{DC}

Vishay Cera-Mite

ORDERING INFORMATION, CERAMIC 6 kV _{DC}							
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE INCH (mm)	WIRE SIZE		ORDERING CODE
					AWG	INCH (mm)	
C0G (NP0)							
10	± 20 %	0.400 (10.2)	0.220 (5.6)	0.375 (9.5)	20	0.032 (0.81)	564R60GAQ10
U2J (N750)							
22	± 20 %	0.460 (11.7)	0.240 (6.1)	0.375 (9.5)	20	0.032 (0.81)	564R60GAQ22
R3L (N2200)							
33	± 20 %	0.400 (10.2)	0.230 (5.8)	0.375 (9.5)	20	0.032 (0.81)	564R60GAQ33
47		0.460 (11.7)	0.205 (5.2)				564R60GAQ47
X5F							
100	± 20 %	0.400 (10.2)	0.240 (6.1)	0.375 (9.5)	20	0.032 (0.81)	564R60GAT10
220			0.265 (6.7)				564R60GAT22
X5S							
330	± 20 %	0.400 (10.2)	0.260 (6.6)	0.375 (9.5)	20	0.032 (0.81)	564R60GAT33
Y5U							
470	± 20 %	0.400 (10.2)	0.265 (6.7)	0.375 (9.5)	20	0.032 (0.81)	564R60GAT47
560			0.240 (6.1)				564R60GAT56
Z5U							
1000	± 20 %	0.400 (10.2)	0.270 (6.9)	0.375 (9.5)	20	0.032 (0.81)	564R60GAD10
1500		0.460 (11.7)	0.280 (7.1)				564R60GAD15
2200		0.530 (13.5)	0.240 (6.1)				564R60GAD22
3300		0.620 (15.7)	0.260 (6.6)				564R60GAD33
4700		0.790 (20.0)					564R60GAD47
0.010 μF		0.950 (24.1)	0.250 (6.4)				564R60GAS10

ORDERING INFORMATION, CERAMIC 7.5 kV _{DC}							
C (pF)	TOL. (%)	D DIAMETER INCH (mm)	T THICKNESS INCH (mm)	LS LEAD SPACE INCH (mm)	WIRE SIZE		ORDERING CODE
					AWG	INCH (mm)	
X5F							
100	± 20 %	0.530 (13.5)	0.310 (7.9)	0.500 (12.7)	20	0.032 (0.81)	564R75GAT10
470		0.620 (15.7)	0.270 (6.9)				564R75GAT47
Y5U							
1000	+ 80/- 20 %	0.620 (15.7)	0.320 (8.1)	0.500 (12.7)	20	0.032 (0.81)	564R75GAD10
Z5U							
2500	+ 80/- 20 %	0.620 (15.7)	0.280 (7.1)	0.500 (12.7)	20	0.032 (0.81)	564R75GAD25



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.