

Cree® 5-mm Round LED Model # LC503FPG1-15Q-A3 Data Sheet

15-degree, 5-mm LED lamp in green color with water-transparent lens and no stopper

Applications

- Advertising Signs
- Indicators
- LCD Back Lights
- Moving-Message Signs

Absolute Maximum Ratings ($T_A = 25^{\circ}C$)

Items	Symbol	Absolute Maximum Rating	Unit	
Forward Current	I _F	25	mA	
Peak Forward Current Note	I _{FP}	100	mA	
Reverse Voltage	V _R	5	V	
Power Dissipation	P _D	100	mW	
Operation Temperature	T _{opr}	-40 ~ +95	°C	
Storage Temperature	T _{stg}	-40 ~ +100	°C	
Lead Soldering Temperature	T _{sol}	Max. 260°C for 3 sec. max. (3 mm from the base of the epoxy bulb)		

Note: Pulse width ≤ 0.1 msec, duty $\leq 1/10$.

Typical Electrical & Optical Characteristics ($T_A = 25^{\circ}C$)

Characteristics	Symbol	Condition	Unit	Minimum	Typical	Maximum
Forward Voltage	V _F	$I_{F} = 20 \text{ mA}$	V		3.2	4.0
Reverse Current	I _R	$V_{R} = 5 V$	А			100
Dominant Wavelength	D	$I_F = 20 \text{ mA}$	nm	520	527	535
Luminous Intensity	I _v	$I_{F} = 20 \text{ mA}$	mcd	16800	34000	
50% Power Angle	2 1⁄2H-H	$I_F = 20 \text{ mA}$	deg		15	



Standard Bins for LC503FPG1-15Q-A3 ($I_F = 20 \text{ mA}$)

Lamps are sorted to luminous intensity (I_v) and dominant wavelength $(_p)$ bins shown.

Orders for LC503FPG1-15Q-A3 may be filled with any or all bins contained as below.

All luminous intensity (I_v) and dominant wavelength ($_D$) values shown and specified are at I_F = 20 mA.



Important Notes:

- 1. All ranks will be included per delivery; rank ratio will be based on the dice distribution.
- 2. Pb content <1000 ppm.
- 3. Tolerance of measurement of luminous intensity is $\pm 15\%$.
- 4. Tolerance of measurement of dominant wavelength is ± 1 nm.
- 5. Tolerance of measurement of $V_{\rm F}$ is ±0.05 V.
- 6. Packaging methods are available for selection; please refer to the "Cree LED Lamp Packaging Standard" document.
- 7. Please refer to the "Cree LED Lamp Reliability Test Standards" document for reliability test conditions.
- 8. Please refer to the "Cree LED Lamp Soldering & Handling" document for information about how to use this LED product safely.



Graphs





Half Power \triangle WL=38nm





300 400 500 600 700 800 FIG.4 RELATIVE LUMINOUS INTENSITY VS. WAVELENGTH.





Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.cree.com/ledlamps



Mechanical Dimensions

All dimensions are in mm. Tolerance is ± 0.25 mm unless otherwise noted.

An epoxy meniscus may extend about 1.5 mm down the leads.

Burr around bottom of epoxy may be 0.5 mm max.



Notes

RoHS Compliance

The levels of environmentally sensitive, persistent biologically toxic (PBT), persistent organic pollutants (POP), or otherwise restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2002/95/EC on the restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS), as amended through April 21, 2006.

Vision Advisory Claim

Users should be cautioned not to stare at the light of this LED product. The bright light can damage the eye.

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.cree.com/ledlamps



Kit Number System

Cree LED lamps are tested and sorted into performance bins. A bin is specified by ranges of color, forward voltage, and brightness. Sorted LEDs are packaged for shipping in various convenient options. Please refer to the "Cree LED Lamp Packaging Standard" document for more information about shipping and packaging options.

Cree LEDs are sold by order codes in combinations of bins called kits. Order codes are configured in the following manner:



* Contact your Cree sales representative for ordering information.

Standard Available Kits*

Kit Number	Description
LC503FPG1-15Q-A3-00001	5mm Round 15 Green , FULL RANK, Bulk Pack
LC503FPG1-15Q-A3-00011	5mm Round 15 Green , Z3 or above, Bulk Pack

* Please contact your Cree representative about the availability of non-standard kits.

Copyright © 2008 Cree, Inc. All rights reserved. The information in this document is subject to change without notice. Cree and the Cree logo are registered trademarks of Cree, Inc.

Cree, Inc. 4600 Silicon Drive Durham, NC 27703 USA Tel: +1.919.313.5300 www.cree.com/ledlamps