



◆ STANDARD SIZE, RATED RIPPLE CURRENT

Cap(μF)	WV ∅ D	200							
		∅ 22		∅ 25		∅ 30		∅ 35	
270		22×25	1.64						
330		22×30	1.89						
390		22×35	2.14	25×25	1.99				
470		22×40	2.41	25×30	2.32	30×25	2.27		
560		22×45	2.71	25×35	2.63	30×25	2.43		
680		22×50	3.06	25×35	2.81	30×30	2.82		
820				25×45	3.32	30×30	2.94	35×25	2.56
1000				25×50	3.72	30×35	3.36	35×30	3.07
1200						30×40	3.78	35×35	3.57
1500						30×50	4.48	35×40	4.01
1800								35×45	4.44
2200								35×50	4.90

Cap(μF)	WV ∅ D	400							
		∅ 22		∅ 25		∅ 30		∅ 35	
82		22×30	0.81						
100		22×35	0.99	25×25	0.99				
120		22×40	1.19	25×30	1.19				
150		22×45	1.43	25×35	1.43	30×25	1.41		
180		22×50	1.60	25×40	1.61	30×30	1.61		
220				25×45	1.83	30×35	1.84		
270				25×50	2.06	30×40	2.10	35×30	2.00
330						30×45	2.36	35×35	2.29
390						30×50	2.62	35×40	2.56
470								35×45	2.86
560								35×50	3.15

Cap(μF)	WV ∅ D	450							
		∅ 22		∅ 25		∅ 30		∅ 35	
68		22×30	0.67						
82		22×35	0.81	25×25	0.81				
100		22×40	0.99	25×30	0.99				
120		22×45	1.19	25×35	1.19	30×25	1.19		
150				25×40	1.49	30×30	1.49	35×25	1.49
180				25×45	1.68	30×35	1.70	35×25	1.61
220				25×50	1.89	30×40	1.92	35×30	1.85
270						30×45	2.18	35×35	2.12
330						30×50	2.45	35×40	2.41
390								35×45	2.67
470								35×50	2.97

↑ Ripple Current (A r.m.s./120Hz, 105°C)
 ↑ Case Size ∅ D×L(mm)