

# Analogue Dial Indicators

## Series 2

Standard size with 0.001 mm graduation



2109 SB-10



2110 SB-10



2110 SB-70

Properties	2109 SB-10	2110 SB-10	2110 SB-70
Continuous scale	●	●	●
Double sided scale	●	●	●
Shock proof	●	●	●
Wide scale spacing	●	●	●
Splash proof	●	●	●
Jewel bearing	●	●	●

### Specifications

Accuracy: Factory specification  
Delivered with factory certificate

Notation "B" = without eyelet

For various accessories see pages 206 and 207.

For special measuring inserts see pages 208 and 209.



No. 2110 SB-70 in stand no. 7002M

Measuring range mm	Graduation mm	No.	Scale	1 Pointer rotation mm	$f_e$ $\mu\text{m}$	$f_{ges}$ $\mu\text{m}$	$f_d$ $\mu\text{m}$	Measuring force max. N	Mass g	Note
1	0,001	<b>2109 SB-10</b>	0-100-0	0,2	3	5	2	1,5	139	☑ ☑ ☑ ☑
1	0,001	<b>2110 SB-10</b>	0-100 (100-0)	0,1	3	5	2	1,5	140	☑ ☑ ☑ ☑
1	0,001	<b>2110 SB-70</b>	0-100 (100-0)	0,1	3	5	2	2,0	141	☑ ☑ ☑ ☑

No. without "B"  $\Delta$  Lid with eyelet supplied

No.	A mm	B mm	C mm	D mm	F mm	G mm	H mm	I mm
<b>2109 SB-10</b>	48,8	60,5	57,0	17,7	16,9	15,1	52	7,6
<b>2110 SB-10</b>	48,8	66,5	57,0	17,7	16,9	21,2	52	7,6
<b>2110 SB-70</b>	48,8	67,5	57,0	17,7	12,3	26,7	52	7,6

