DURACELL[®] Rechargeable



Rechargeable D





Dimensions shown are IEC standards

Product can be charged on most NiMH or NiCd chargers utilizing standard dV, dV/dt, time and temperature dynamic charge termination methods. Duracell brand NiMH chargers are recommended for best results.

Delivered capacity is dependent on the applied load, operating temperature, and cut-off voltage. Please refer to the charts and discharge data shown for example of the energy/service life that the battery will provide for various local conditions.

This data is subject to change. Performance information is typical. Contact Duracell for latest information.

BENEFITS

• Reliable Performance in Everyday Devices!

TECHNICAL

Type: Nominal Voltage Nominal Internal Impedance: Average Weight: Volume: Operating Temperature Range: ANSI: IEC: Product Codes NiMH D 2200 mAh 1.2V 45 m-ohm @ 1 kHz 71.0 grams (2.5 ounces) 56.4 cm³ (3.44 in³) -20° C to 50° C (-4° F to 122° F) 1.2H4 HR20 Blister x2 EU/UK SAP Code: 75052461 EU/UK EAN Code: 5000394055995







