







MOUNTING HOLE

Electrical Characteristics

Nominal Impedance: 50 ohms
Frequency Range: DC to 4 GHz
Insertion Loss: 0.2 dB at 3 GHz
Operating Voltage (rms): 500 V maximum at sea level
Dielectric Withstand Voltage (rms): 1500 V maximum at sea level
Contact Resistance: 1.5 milliohms maximum
Insulation Resistance: 5000 megohms minimum

Mechanical Characteristics

Mating Cycles: 500 cycles minimum
Interface Dimensions: Conform to MIL-C-39012

Environmental Characteristics

Temperature Range: -65 °C to +165 °C

PART	DESCRIPTION
1	Body
2	Nut
3	Washer
4	Dielectric
5	Body
6	Pin

Dimensional changes	MS	4	7 Jan 09
Dimensional changes	SN	3	22 Nov 01
CAD Issue	SN	2	06 Nov 01
First Issue	AT	1	13 Feb 96
DESCRIPTION OF REVISION	APPVD	ISS	DATE

TITLE:

Isolated BNC Panel Mount
Jack

PART NUMBER:

VB11094A

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:

± 0.2mm unless
otherwise stated

DRAWN BY:

S Nash

CHECKED BY:

M Nielsen

APPROVED BY:

P Couzens

DATE:

22 Nov 01



EMERSON
Network Power

Connectivity Solutions
7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 359938