



MOUNTING HOLE



Electrical Characteristics

Nominal Impedance:	75 ohms
Frequency Range:	DC to 1 GHz
Insertion Loss:	0.2 dB at 1 GHz
Operating Voltage (rms):	500 V maximum at sea level
Dielectric Withstand Voltage (rms):	1500 V maximum at sea level
Contact Resistance:	1.5 milliohms maximum
Insulation Resistance:	5000 megohms minimum

Mechanical Characteristics

Mating Cycles:	500 cycles minimum
Interface Dimensions:	Conform to MIL-C-39012

Environmental Characteristics

Temperature Range:	-20 °C to +80 °C
--------------------	------------------

PART	DESCRIPTION
1	Body 1
2	Nut
3	Washer
4	Dielectric
5	Body 2
6	Contact

Dimensions updated	MS	3	14 Apr 09
CAD Issue	SN	2	11 Feb 02
First Issue	AT	1	02 Dec 99
DESCRIPTION OF REVISION	APPVD	ISS	DATE

PART NUMBER:

VB11094A-75

Isolated BNC Panel Mount Jack

SCALE: Not To Scale

DIMENSIONS: mm

CHECKED BY:

S Nash

APPROVED BY:

P D Couzens

TOLERANCES:
± 0.2mm unless
otherwise stated

DATE:

30 May 02



Connectivity Solutions

7-13 Russel Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.

Tel: +44 (0) 1245 359515

Fax: +44 (0) 1245 358938

EMERSON™

Network Power