





REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUES\DATE



RECOMMENDED
CABLE STRIPPING DIM'S



STAMP (IF ANY)

- 1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
- 2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
- 1. BRASS PER QQ-B-626
 - 2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - 3. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
 - 4. TEFLON MIL-P-19468

DIMENSIONS ARE IN MILLIMETERS						PART NO. RT6121A1-NT3G-1-50		<h1 style="text-align: center;">Amphenol</h1>			
UNLESS OTHERWISE SPECIFIED TOLERANCES						APPROVED	DATE			TITLE	
0.5-6 = ±0.2						CHECKED	DATE			TNC REVERSE POLARITY CRIMP JACK	
6-30 = ±0.4						DRAWN	DATE			DRAWING NO.	
5	FERRULE	COPPER	NOTE 2	1	FR-648/533X 127C	10-11-01'		KJ-RT6121A1-NT3G-58CU-50			
4	CONTACT PIN	NOTE 1	NOTE 2	1	RT6121A1-4-25 /11-B	10-11-01'		ITEM NO.			
3	INSULATOR	NOTE 4	NATURAL	1	RT6121A1-3T-50	10-11-01'					
2	BODY	NOTE 1	NOTE 2	1	RT6421G1-2	10-11-01'					
1	HOUSING	NOTE 1	NOTE 2	1	B70000-1-46/31	10-11-01'					
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	A	FILE NO.	