


1 2 3 4 5 6 7 8

REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE
B	A-3	NO.1 WAS CHANGED\RD-DM89042001C\08-20-04'



NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BRASS PER QQ-B-626
2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
3. BERYLLIUM COPPER PER QQ-C-530
4. GOLD PL. 50 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
5. TEFLON MIL-P-19468

					DIMENSIONS ARE IN MILLIMETERS				PART NO.		Amphenol Danbury,CT,USA-Tainan,Taiwan-Shenzhen,China			
					UNLESS OTHERWISE SPECIFIED TOLERANCES				APPROVED	DATE			TITLE	
6	CONTACT PIN	NOTE 1	NOTE 4	1	SMAM-RSMAM-6	0.5-6 = ±0.2	6-30 = ±0.4	30-120 = ±0.6	120-315 = ±1	315-1000 = ±1.6	1000-2000 = ±2.4	SCOTT.H	08-20-04'	SMA MALE TO SMA REVERSE POLARITY MALE ADAPTOR
5	GASKET	SILICONE	RED	1	GS-6/43X06							SCOTT.H	08-20-04'	
4	RETAINER RING	NOTE 3	NATURAL	1	SMA5000-4-B									
3	INSULATOR	NOTE 5	NATURAL	2	SMA5071A1-3T-50									
2	BODY	NOTE 1	NOTE 2	1	SMA5071A1-2-B									
1	SHELL	NOTE 1	NOTE 2	1	SMA5000-1-C									
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	5/1	ISSUE	B	FILE NO.	F:\DWG\SMAM\RSMAM\50\3GT50G	EMPA	08-20-04'	DRAWING NO. SMAM-RSMAM-3GT50G-50
														ITEM NO. 11M-61M1-GA-5-F

7RD-DR 6775358