



注) NOTE.

1. 各部のそりは0.5最大 WARPING:0.5MAX.
2. サークットNO. はNO. " 1" のみ表示  
CIRCUIT NO. : "I" ONLY

10-22-1092	5198-09	45.72	50.72	9
▲ -1082	▲ -08	40.64	45.64	8
-1072	-07	35.56	40.56	7
-1062	-06	30.48	35.48	6
-1052	-05	25.4	30.4	5
-1042	-04	20.32	25.32	4
▼ -1032	▼ -03	15.24	20.24	3
10-22-1022	5198-02	10.16	15.16	2
EDP.NO.	ENG.NO.	B	(A)	極数 CKT.

MATERIAL  
NYLON66, 94V-2

REVISED EC NO: J2007-1223 DRWRT:SUROKA 2006/10/30 CHKDK: TOYODA 2006/10/31 APP: NUKITA 2006/10/31	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY	SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
	10 UNDER	±0.2	DRAWN BY K. KOHAMA	DATE '00/03/28	TITLE SPOX 10.16/5.08 PITCH REC HSG	
	10 OVER 30 UNDER	±0.25	CHECKED BY T. YAMAGUCHI	DATE '00/03/30	MOLEX INCORPORATED	
	30 OVER	±0.3	APPROVED BY M. FUKUSHIMA	DATE '00/03/30	DOCUMENT NO. SD-5198-001	SHEET NO. 1 OF 1
	ANGULAR ±3 °	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO. 5198-**			
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					