

SUHNER® COAXIAL CONNECTOR DATA SHEET TYPE 24_QMA-50-3-3/111_N

Description

Straight panel bulkhead cable jack, flange mount

QuickLock Interface



General Information

Cable

Cable Entry

Electrical Data Impedance: Interface frequency max.:

Piece Parts Center contact: Outer contact:

Insulator:

Body:

Fastening nut: Gasket: Washer:

Attachments

Notes

WAIVER! While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be constructed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.

Issued: 11.02.04 15:06		Document: DOC-0000185154
RF_Ca_Pa_C_PDF	uncontrolled copy	Page 1

QMA Interface dims acc. to: Weight:

Cable type: Cable type: Cable type:

Centre contact: Outer contact:

50Ω

18 GHz

Bronze

Brass

Brass

Brass

Bronze

Material

PFA / PTFE

MQ (Silicon Rubber)

Outline drawing:

Mounting hole:

Catalogue drawing:

Assembly instruction:

0.0042 Kg / 0.15 oz

SM_141 EZ_141-TP/M17 MF_141

SUHNER-QMA

plugged soldered

Surface Plating SUCOPRO Plating SUCOPRO Plating SUCOPRO Plating

SUCOPRO Plating

SUCOPRO Plating

DOU-00008996 DCA-00008998 DOC-0000179521 DOU-00008748

H HUBER+SUHNER

HUBER+SUHNER AG Interconnect Division CH-9100 Herisau Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 http://www.hubersuhner.com



SUHNER® COAXIAL CONNECTOR DATA SHEET

Order as **24_QMA-50-3-3/111_NE** for Order as **24_QMA-50-3-3/111_NH** for

for Single for Bulk 100 pcs



HUBER+SUHNER AG Interconnect Division CH-9100 Herisau Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 http://www.hubersuhner.com

Issued: 11.02.04 15:06		Document: DOC-0000185154
RF_Ca_Pa_C_PDF	uncontrolled copy	Page 2