





NO	DESCRIPTION	DATE
△	ADD STRIPPING DIMENSION BACKGROUND FORMAT UPDATED	03.02.10'



△ STRIPPING DIMENSION

1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-900 MHz
- 1.2 NOMINAL IMPEDANCE: 50 OHM

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
- 2.4 CRIMP FERRULE: BRASS PER JIS-C2700

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 FOR USE WITH RG58U OR SIMILAR STYLE CABLE
- 4.2 CABLE ATTACHMENT: OUTER: CRIMP, INNER: SOLDER/CRIMP
- 4.3 CRIMP SIZE REQUIRED: CONTACT: SOLDER/1.8(071) HEX. CRIMP TOOL
FERRULE: 5.5(215) HEX. CRIMP TOOL

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -55° C TO +125° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
5	INSULATION	TEFLON	1	NONE
4	BODY	BRASS	1	NICKEL 100μ" MIN.
3	INSULATION	TEFLON	1	NONE
2	CENTER CONTACT	BRASS	1	GOLD
1	CRIMP FERRULE	BRASS	1	NICKEL 100μ" MIN.

APPROVED by _____ DATE: _____

DESCRIPTION		FME STRAIGHT PLUG CRIMP								
製圖	DRAWN	TOLERANCE		品名	23-07	T.G.N 58U	日期	DATE	版次	REV.
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT (50μ)		09.30.92'		A-1	
檢圖	CHECK	.XX	±0.1	單位	UNIT	DWG.NO.		23-0032		
	Jacky	.XXX	±0.05	mm(in)	SCALE					
認定	APPROVAL	ANGLE	±5°	比例	SCALE	佳楠精密電子股份有限公司				
	Lewis			4:1	CHIN NAN PRECISION ELECTRONICS CO.,LTD.					