

**XL20
Supreme Magnifier - IP20**



- Illuminated general purpose magnifier fitted with fully spring balance arm for ease of movement
- Parallel motion maintains head position during movement
- Available in 2 versions Bench version or complete with table base
- 22 watt circular fluorescent lamp - fitted with tube protection cover
- 127mm diameter viewing lens - 3 diopter (1.75 times magnification) fitted as standard - higher dioptr lens available up to 15 are available as replacement or factory fitted
- Bench version complete with table clamp - optional wall or floor trolley mounts available

Articulated Friction Arm Solutions



- Friction jointed Armadapt for a variety of uses in industry and commerce
- Joints can be adjusted and set in position easily
- 4 standard arm configurations
- Variants to customer requirements (subject to qty)
- Alternative mounting options i.e. spigots etc
- Bench clamp available as optional extra
- Standard colour - Gunmetal other finishes and colours to order (subject to qty) i.e. Chrome, white powder coated etc

**XL11
Superior Magnifier - IP20**



- Illuminated magnifier fitted with fully spring balance arm for ease of movement
- Parallel motion maintains head position during movement
- Available in 2 versions Bench version or complete with table base
- 2 x 9watt fluorescent lamps - fitted with tube protection covers
- 200mm x 152mm viewing lens - 3 diopter (1.75 times magnification) fitted as standard - higher dioptr lens available up to 15 are available as replacement or factory fitted
- Bench version complete with table clamp - optional wall or floor trolley mounts available

Superglide Trolley



- High specification heavy duty floor trolley
- Suitable for wide range of industrial and medical uses
- Suitable for all EDL luminaires fitted with universal base when used in conjunction with spigot adaptor.
- Spigot on spring arm units (i.e. magnifiers & XL51) will fit directly into trolley pole
- Base size 660mm - Pole height 1000mm
- Heavy weighted base and long reach feet provide impressive stability
- Anti static castors 50mm diameter (75mm castors available)

**XL11
Superior Magnifier - IP20**



- Balance arm for ease of movement
- 127mm diameter viewing lens - 3 diopter (1.75 times magnification) fitted as standard
- Supplied with multi-purpose clamp - can be used for wall, desk or screw down mounting
- ES lampholder (E27) fitted - maximum 60 watt candle lamp
- Available in Black or White
- Optional table base available



Lighting Ltd.
Medical Surgical & Industrial



Lighting Ltd.
Medical Surgical & Industrial



Redbrook Lane, Brereton,
Rugeley, Staffs, WS15 1QU.

Tel: 01889 582112

Fax: 01889 584012

www.edl-lighting.co.uk
e-mail: sales@edl-lighting.co.uk

Company Resgistered in England No: 3772991



Industrial Lighting

The original EDL was formed in Birmingham in 1922. Since then, through the years with subsequent name changes and owners, it reverted back to EDL in 1999 and became EDL Lighting Limited, to ensure continuation of the well established brand name.

All lighting products are designed and manufactured in accordance with B.S. EN 60598. The company is an active member of the Lighting Association and adheres to their Manufacturing Code of Practice

A design and build facility for task lighting products and support arm solutions is available along with variants of our existing product range. For full details of our product range please refer to web site.

We would be only to pleased to discuss your requirements, please call, fax or e mail us in the first instance
EDL also manufactures and supplies a range of medical and surgical lighting products

Task One - IP20



- Is a general purpose machine or bench light
- Available with 5 different arm configurations.
- Can be used on mains or low voltage
- Can be used in conjunction with the MT series of transformers
- Universal mount for vertical or horizontal mounting
- Edison screw lampholder (E27) particularly suitable for vibratory conditions
- Colour - Goosewing Grey powder coated

Loading Bay - IP44



- Long reach 55w or 70w luminaire
- Arm Length 400mm + 400mm + 400mm or Head to Base unit (no arms)
- Powerful 12v 55w or 24v 70w halogen lamp supplied
- Can be used in conjunction with the MT series of transformers (for low voltage supply)
- Universal mount for vertical or horizontal mounting

Haloflex - IP21 Flexible



- Ideal for variety of applications including machine tools, wood working, general bench illumination and many commercial applications
- Input voltages 12v, 24v, 110v & 240v
- Flexible arm either 150mm or 700mm long
- Switch fitted on head for ease of use
- Can be screwed to bench/machine or used with alternative accessories (magnetic base, wall bracket or desk clamp)
- Protective lens cover available

Kaliflex - IP41



- Based on Haloflex with 11 watt compact fluorescent lamp fitted
- Switch fitted on head for ease of use
- Can be screwed to bench/machine or used with alternative accessories (magnetic base, wall bracket or desk clamp)
- Flexible arm 700mm long
- Input voltage 240v
- Suitable for offices, bench lighting, inspection, study rooms & a variety of other applications

Haloflex - IP54 Flexible



- Ideal for variety of applications including machine tools, wood working, general bench illumination and many commercial applications
- Fitted with protective lens cover
- Input voltages 12v, 24v, 110v & 240v
- Flexible arm either 150mm or 700mm long
- Switch fitted on head for ease of use
- Can be screwed to bench/machine or used with alternative accessories (magnetic base, wall bracket or desk clamp)

Tube Light - IP67



- Waterproof light with many commercial applications including machine, marine & areas where water and dust are present
- Suitable for machine mounting (withstands coolant spray on light)
- Impact resistant polycarbonate tube 60mm or 80mm diameter
- Input voltage 12v, 24v 110v & 240v
- Fluorescent lamp wattage single 11 to 58 watts, twin 36 & 55 watt compact lamps
- Standard magnetic & electronic ballasts supplied as standard (internal and external along with mounting brackets)
- Variants of standard models are available

Task 21 - IP54



- Is a general purpose IP64 machine or bench light
- Available with 3 different arm configurations.
- Can be used on mains or low voltage
- Can be used in conjunction with the MT series of transformers
- Universal mount for vertical or horizontal mounting
- Edison screw lampholder (E27) particularly suitable for vibratory conditions
- Bench clamp available as optional extra

Task 28 - IP54



- Versatile 18 watt compact fluorescent machine or bench lamp
- Arm length 400mm + 400mm
- Available with standard magnetic ballast or High frequency electronic ballast
- Universal mount for vertical or horizontal mounting
- Bench clamp available as optional extra

XL51 Sovereign - IP20



- Twin 15 watt lamps fitted (equivalent to 150 watts incandescent)
- Fully spring balanced arm - 1100mm long - providing ease of movement whilst maintaining set position
- Parallel motion maintains head position during adjustment
- Complete with table clamp - optional screw down base, wall bracket and floor trolley available

Task 23 - IP64




- Is a general purpose fluorescent IP64 machine or bench light
- Arm length 400mm + 400mm
- 13w or 18 watt energy saving version available with standard magnetic ballast or High frequency electronic ballast
- Universal mount for vertical or horizontal mounting
- Bench clamp available as optional extra

Task 27 IP20 or IP54




- Is a general purpose 16w or 28 watt 2D fluorescent machine or bench light
- Arm length 400mm + 400mm
- Input voltage 240 volt
- Prismatic shield with flexible visor
- Universal mount for vertical or horizontal mounting
- Bench clamp available as optional extra
- 190mm 16w and 270mm 28w diameter metal spun shade

MT Transformer - IP65



- Designed for use with Task 1, Task 21, Task 22 NT, Task 24NT, Task 5ENT and Loading Bay (NT designates no internal transformer)
- High specification, low voltage operation for many industrial applications
- Primary voltage 240v or 415 volt
- Secondary tapping's 12v, 24v, 25v or 50 volts
- Optional mounting brackets available

Task 5E - IP44



- Is a general purpose 50 watt halogen IP44 machine or bench light
- Available with or without integral transformer (ref NT) where low voltage supply is already available
- Input voltages 12v, 24v or 240 volt
- 127mm diameter metal shade with sturdy high impact plastic handle
- Switch mounted on head for ease of use
- Can be used in conjunction with the MT series of transformers (for low voltage)
- Universal mount for vertical or horizontal mounting
- Bench clamp available as optional extra

Task 24 - IP64



- Is a general purpose 50 watt halogen IP64 machine or bench light
- Available with or without integral transformer (ref NT) where low voltage supply is already available
- Can be used in conjunction with the MT series of transformers (for low voltage)
- Universal mount for vertical or horizontal mounting
- Bench clamp available as optional extra

'C' Clamp



- For use with universal Base
- Padding beneath jaw prevents surface marking
- Extruded aluminium 7mm thick
- Jaw opening range 6 - 60mm
- All colours available to suit all EDL Luminaires fitted with universal base